

# Solenoid operated valves

## 2-way 2-positions



Special cavity

Cartridge style in manifold

VEI-CS-8A-06

OS.15 - K - 19 - Y - Z - W

### Dimensions



### Cartridge schemes

monodirectional type	bidirectional type

### Technical data

Max flow:	up to 40 l/min	(11 gpm)
Max operating pressure for <b>steel</b> body:	350 bar	(5000 psi)
Max operating pressure for <b>aluminium</b> body:	210 bar	(3000 psi)

To order only manifold see data sheet RE 18325-85



Performance graphs

