

# Relief, direct acting guided poppet type Special cavity, 008

## VS-30



### Description

Flow is blocked from 1 to 2 until pressure increases to meet the selected valve setting, lifting the poppet from its seat and allowing relief flow through port 2 to tank. Pressure at port 2 is additive to the relief setting of the valve. The unique Bosch Rexroth Oil Control poppet design provides enhanced stability at all flows and pressures. 04.11.18 - X - 99 - Z

**RE 18318-23** Edition: 01.2019 Replaces: 07.2018


Technical data		
Max. operating pressure port 1 (P)	350 bar (5000 psi)	
Max. pressure admitted port 2 (T)	140 bar (2000 psi)	
Max. flow	30 l/min (8 gpm)	
Max. internal leakage <sup>1)</sup>	15 drops/min.	
Fluid temperature range	-30 to 100 °C (-22 to 212 °F)	
Installation torque	45 - 50 Nm (33 - 37 ft-lbs)	
Weight <sup>2)</sup>	0.17 kg (0.38 lbs)	
MTTFD	150 years see RE 18350-51	
Special cavity	008 (see data sheet 18325-75)	
Lines bodies and standard assemblies	Please refer to section "Hydraulic integrated circuit" or consult factory	
Seal kit <sup>3)</sup>	Code: RG0008010000100	
	material no: R930001692	
Fluids	Mineral-based or synthetics with lubricating properties at viscosities of 10 to 500 mm <sup>2</sup> /s (cSt)	
Recommended degree of fluid contamination	Nominal value max. 10µm (NAS 8) / ISO 4406 20/18/15	
Installation position	No restrictions	
Other Technical Data	See data sheet 18350-50	


1) At 80% of pressure setting


2) Standard version 03 type


3) Only external seals for 10 valves

#### **Characteristic curve**










Note: Special settings available. Contact factory authorized representative for ordering code.

\* minimum pressure setting intended with Q=5 l/min

#### **Preferred types**

Туре	Material number	Туре	Material number
041118039905000	R901113613	041118049905000	R930000148
041118039910000	R901113614	041118049910000	R930000149
041118039920000	R901226876	041118049920000	R901127942
041118039935000	R901113617	041118049935000	R930000151

#### **Dimensions**



Bosch Rexroth Oil Control S.p.A. Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.