

Logic element, direction control poppet type Common cavity, Size 10

VLDT-10A

04.84.07 - X - 85 - Z

RE 18321-76Edition: 03.2016
Replaces: 01.2010





Description

Flow is blocked bi-directionally between 1 and 2, until pressure at either 1 or 2 rises above the combined pressure of the spring bias, plus pressure at 3. The poppet is balanced between pressures at 1 and 2 with a 1:1 area ratio, and held locked by pressure at 3 in a 2:1 ratio versus either 1 or 2.


| Technical data | |
|---|--|
| Max. operating pressure | 350 bar (5000 psi) |
| Max. flow | 80 l/min. (21 gpm) |
| Pilot ratio | 2:1 |
| Max. internal leakage | 5 drops/min. at 200 bar (2900 psi) closed |
| Fluid temperature range | -30 to 100 °C (-22 to 212 °F) |
| Installation torque | 41 - 47 Nm (30 - 35 ft-lbs) |
| Weight | 0.12 kg (0.27 lbs) |
| Cavity | CA-10A-3C (see data sheet 18325-70) |
| Lines bodies and standard assemblies | Please refer to section "Hydraulic integrated circuit" or consult factory |
| Seal kit ¹⁾ | Code: RG10A9010530100 |
| | material no: R901111368 |
| Fluids | Mineral-based or synthetics with lubricating properties at viscosities of 5 to 800 mm²/s (cSt) |
| Recommended degree of fluid contamination | Nominal value max. 10µm (NAS 8) / ISO 4406 19/17/14 |
| Installation | No restrictions |
| Other Technical Data | See data sheet 18350-50 |


¹⁾ Only external seals for 10 valves





Characteristic curve






Preferred types

| Туре | Material number | Туре |
|-----------------|-----------------|------|
| 048407008504000 | R901095969 | |

| Туре | Material number |
|------|-----------------|
| | <u> </u> |

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5
P.O. Box no. 5
41015 Nonantola – Modena, Italy
Tel. +39 059 887 611
Fax +39 059 547 848
compact-hydraulics-cv@boschrexroth.com
www.boschrexroth.com/compacthydraulics

® This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.