

Directional spool type, direct acting, external pilot internal drain Common cavity, Size 10

VDSB-10A-6



Description

Flow is allowed from 2 to 3 until the pressure at 1 rises to the selected spring setting. Upon reaching this pressure, the spool shifts upward, blocking flow until pressure at 1 drops below the set point. The spring chamber is drained to 3, thus any pressure at 3 is additive to the spring setting.

VDSB-10A-6 is especially designed for application requiring high value of shifting pressure.

04.77.23 - X - 85 - Z


RE 18320-74


Edition: 03.2016 Replaces: 10.2009

Technical data		
Technical data		
Max. operating pressure	350 bar (5000 psi)	
Max. flow	30 l/min. (8 gpm)	
Max. internal leakage ¹⁾	10 cm³/min. (0.6 cu.in./min.)	
Fluid temperature range	-30 to 100 °C (-22 to 212 °F)	
Installation torque	41 - 47 Nm (30 - 35 ft-lbs)	
Weight	0.27 kg (0.6 lbs)	
Cavity	CA-10A-3N (see data sheet 18325-70)	
Lines bodies and standard	Please refer to section "Hydraulic	
assemblies	integrated circuit" or consult factory	
Seal kit ²⁾	Code: RG10A3010520100	
	material no: R901111369	
Fluids	Mineral-based or synthetics with lubricating properties at viscosities of	
	10 to 500 mm ² /s (cSt)	
Recommended degree of	Nominal value max. 10µm (NAS 8) /	
fluid contamination	ISO 4406 19/17/14	
Installation position	No restrictions	
Other Technical Data	See data sheet 18350-50	


1) Measured at 200 bar (2900 psi)


2) Only external seals for 10 valves





Characteristic curve






for ordering code.

Preferred types

Material number	Туре	Material number	
R901109479			
R901109481			
R901109482			
	R901109479 R901109481	R901109481	

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.