


Dual cross over relief, direct acting, flangeable to motor

VSDI-30-FM



Description

It relieves the inlet pressure from either one of the supply lines and it protects the motor from shocks or pressure surges induced by changes in direction or by sudden stops. The dual relief is of the cross over type, and exhausted oil is transferred to the other line (from V1 into V2 and viceversa), without the necessity of a separate tank line: this feature also prevents cavitation when used in conjunction with closed centre directional valve.

05.16.17 - X - Y - Z


RE 18308-17 Edition: 03.2016 Replaces: 11.2015

Technical data


Operating pressure	up to 210 bar (3000 psi)	
Max. flow	30 l/min. (8 gpm)	
Weight	0.9 kg (1.98 lbs)	
Manifold material	Aluminium	
Note: aluminium bodies are often pressures exceeding 210 bar (3) fatigue life expected in the speci our Service Network.		
Flange seal kit ¹⁾	E0000000000032 (R930005697)	
Flangeable on SAUER-DANFOSS	orbital motors OMS series	
For relief cartridge details, see F	RE 18318-23 (VS-30 041118X99Z)	
Each cartridge can be individual	ly pressure set.	
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	10 to 500 mm ² /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
Other technical data	see data sheet 18350-50	


Note: for applications outside these parameters, please consult us.

¹⁾ Seal for 10 valves




Characteristic curve





Туре	Material number	Туре	Material number
05161703032000A	R930008288		

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.