


Motion control dual setting

VAA-B-SICN-PDRM-150

RE 18308-79

Edition: 03.2016

Replaces: 07.2012



Description

It provides static and dynamic motion control by regulating flow and pressure IN and OUT of the hydraulic motor at ports C1 and C2. When installed close to the motor, it can stop runaway in case of hose failure. The check sections allow free flow into the motor and prevent reverse movement; the pilot assisted relief valves control the movement when pilot pressure is applied. The relief valves operate with 2-levels pressure setting, both adjustable: higher setting when flow is delivered to the motor, and lower setting when flow is discharged by the motor during stopping. A system of check valves allows cross line relief and an optional make-up port (T) allows to compensate for any volume change.

Technical data

05.71.46 - X - 04 - Z


Operating pressure	up to 210 bar (3000 psi)
Max. flow	120 l/min. (32 gpm)
Weight	5.7 kg (12.6 psi)
Manifold material	Aluminium

Note: aluminium bodies are often strong enough for operating pressures exceeding 210 bar (3000 psi), depending from the fatigue life expected in the specific application. If in doubt, consult our Service Network.


Fluid	Mineral oil (HL, HLP) according DIN 51524
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)
Viscosity range	10 to 500 mm ² /s (cSt)
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406
Other technical data	see data sheet 18350-50

Relief setting: at least 1.3 times the highest expected load. The lower pressure setting (see table "SPRINGS") refers to flow "C1" to "C2" (or "C2" to "C1"), and is adjustable through register "A" (see the drawing).

Note: for applications outside these parameters, please consult us.



Characteristic curve




2

Ordering co	ode	05.71.4	46 X	04	Z			
Motion contr	ol dual settir	ng					SPRINGS	
						Adj. pressure	Pres. increase	Std. setting
Dilet metic						range	bar/turn	Q=5 (I/min)
Pilot ratio						bar (psi)	(psi/turn)	bar (psi)
				35	100-350	100	300 (4350)	
03 7.6:1				35	(1450-5000)	(1450)	120* (1740)	
					* Low	er pressure setting.		
Port sizes V1 - V2 C1 - C2 T					Tamper resistant cap code ordering code 03.05.01.001 Mat. no. R930000470			
	G 3/4	G 3/4	G 1/2					

Preferred types

Туре	Material number	Туре	Material number
05714603043500C	R930006980		
		•	

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5

41015 Nonantola – Modena, Italy

Tel. +39 059 887 611 Fax +39 059 547 848

compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics

® This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.