


Dual counterbalance, relief compensated

A-VBSO-DE-CC



Description

It provides static and dynamic control of load by regulating the flow IN and OUT of the actuator, through ports C1 and C2. This valve module includes 2 sections, each one composed by a check and a relief valve with balanced piston, pilot assisted by pressure in the opposite line: the check section allows free flow into the actuator, then holds the load against reverse movement; with pilot pressure applied at the line across, the pressure setting of the relief is reduced in proportion to the stated ratio until opening and allowing controlled reverse flow. Relief operates at the valve setting independent of back-pressure, but the piloted opening remains subject to additive pressure at V1 or V2.




RE 18307-69 Edition: 03.2016 Replaces: 10.2009


Technical data


Max. operating pressure	350 bar (5000 psi)	
Max. flow	see performance graph	
Weight	4.5 kg (9.9 lbs)	
Manifold material	Zinc plated steel	
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	5 to 800 mm ² /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
Other technical data	see data sheet 18350-50	

Note: for applications outside these parameters, please consult us.



Characteristic curve






Preferred types

Туре	Material number	Туре	Material number
084205020435000	R930001126		

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.