
Rexroth Bosch Group


Motion control, dual setting with brake release port

VAA-B-SICN-PDRM-VF-150



Description

It provides static and dynamic motion control by regulating flow and pressure IN and OUT of the hydraulic motor at ports C1 and C2. When installed close to the motor, it can stop runaway in case of hose failure. The check sections allow free flow into the motor and prevent reverse movement; the pilot assisted relief valves control the movement when pilot pressure is applied. The relief valves operate with 2-levels pressure setting, both adjustable: higher setting when flow is delivered to the motor, and lower setting when flow is discharged by the motor during stopping. A system of check valves allows cross line relief and an optional make-up port (T) allows to compensate for any volume change. Through port C3, a shuttle valve directs either V1 or V2 pressure to the spring actuated brake for brake releasing.



05.71.47 - X - 04 - Z

RE 18308-82 Edition: 03.2016 Replaces: 07.2012


Technical data


Operating pressure	up to 210 bar (3000 psi)		
Max. flow	120 l/min. (32 gpm)		
Weight	5.7 kg (12.6 psi)		
Manifold material	Aluminium		
Note: aluminium bodies are often strong enough for operating pressures exceeding 210 bar (3000 psi), depending from the fatigue life expected in the specific application. If in doubt, consult our Service Network.			
Fluid	Mineral oil (HL, HLP) according DIN 51524		
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)		
Viscosity range	10 to 500 mm ² /s (cSt)		
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406		
Other technical data	see data sheet 18350-50		
Relief setting: at least 1.3 times th	highest expected load.		

Relief setting: at least 1.3 times the highest expected load. The lower pressure setting (see table "SPRINGS") refers to flow "C1" to "C2" (or "C2" to "C1"), and is adjustable through register "A" (see the drawing).

Note: for applications outside these parameters, please consult us.

Characteristic curve






Preferred types

Туре	Material number	Туре	Material number
05714703043500B	R930006860		

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.