


# Dual counterbalance

RE 18308-63

Edition: 03.2016 Replaces: 07.2012


A-VBSO-DE-90-FC2



#### **Description**

It provides static and dynamic control of load by regulating the flow IN and OUT of the actuator, through ports C1 and C2. This valve module includes 2 sections, each one composed by a check and a relief valve pilot assisted by pressure in the opposite line: the check section allows free flow into the actuator, then holds the load against reverse movement; with pilot pressure applied at the line across, the pressure setting of the relief is reduced in proportion to the stated ratio until opening and allowing controlled reverse flow. Back-pressure at V1 or V2 is additive to the pressure setting in all functions. For better safety and compact assembly, the C1 and C2 ports are gasket mounted directly on the actuator.

Note: port identified with M are not protected with calibrated orifice but in direct connection with pressure channels.




## **Technical data**

08.44.89 - X - Y - Z

Max. operating pressure	410 bar (5945 psi)
Max. flow	90 l/min. (24 gpm)
Weight	3 kg (6.6 lbs)
Manifold material	Zinc plated steel
Flange seal kit 1)	E00000000000009 (R930004539)
Fluid	Mineral oil (HL, HLP) according DIN 51524
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)
Viscosity range	5 to 800 mm <sup>2</sup> /s (cSt)
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406
Other technical data	see data sheet 18350-50
Relief setting: at least 1.3 times the highest expected load.	

Note: for applications outside these parameters, please consult us.

## Characteristic curve



<sup>1)</sup> Seals for 5 valves.

# A-VBSO-DE-90-FC2 | Dual counterbalance

	_			
Ordering co	ode	08.44.8	39 X	Υ
Dual counter	balance			
Pilot ratio				
<b>03</b> 4.2	: 1			
Port sizes	V1 - V2	C1 - C2	M1 - M	2
03	G 1/2	Ø 9 (0.35)	G 1/4	

	SPRINGS		
	Adj. pressure	Pres. increase	Std. setting
	range	bar/turn	Q=5 (I/min)
	bar (psi)	(psi/turn)	bar (psi)
35	180-350	138	350
33	(2610-5000)	(2001)	(5000)

Pressure setting up to 410 bar: code on request.

Tamper resist ordering code	ant cap code e 11.04.23.002	
Mat. no.	R930000752	

Z


# **Preferred types**

2

Туре	Material number
084489030335000	R930003459

Туре	Material number

#### **Dimensions**



## Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5

41015 Nonantola – Modena, Italy

Tel. +39 059 887 611 Fax +39 059 547 848

compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics

® This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.