


Single counterbalance

RE 18307-38

Edition: 02.2022

Replaces: 03.2016

A-VBSO-SE-30-FC1



Description


When pressure at V2 rises above the spring bias pressure, the check seat is pushed away from the piston and flow is allowed from V2 to C2. When load pressure at C2 rises above the pressure setting, the direct operated relief function is activated and flow is relieved from C2 to V2. With pilot pressure at Pil, the pressure setting is reduced in proportion to the stated ratio of the valve, until opening and allowing flow from C2 to V2. The spring chamber is drained to V2, and back-pressure at V2 is additive to the pressure setting in all functions. For safety and compactness, the C2 port is gasket mounted the actuator.

Technical data


08.41.02 - X - Y - Z

Max. operating pressure	410 bar (5945 psi)	
Max. flow	60 l/min. (16 gpm)	
Weight	1.05 kg (2.3 lbs)	
Manifold material	Zinc plated steel	
Flange seal kit ¹⁾	E00000000000056 (R930060579)	
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	5 to 800 mm ² /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
MTTFd	150 years see data sheet 18350-51	
Other technical data	see data sheet 18350-50	
Relief setting: at least 1.3 times the load induced pressure.		

Note: for applications outside these parameters, please consult us.



Characteristic curve



¹⁾ Seals for 10 valves.

A-VBSO-SE-30-FC1 | Single counterbalance

Ordering code		08.41.0	02	Х	Υ
Single count	erbalance				
Pilot ratio					
03 4.2	: 1				
Port sizes	V2	C2		Pil	
09	G 1/4	Ø 9 (0.35)	(à 1/4	
02	G 3/8	Ø 9 (0.35)		3/8	

	SPRINGS		
	Adj. pressure	Pres. increase	Std. setting
	range	bar/turn	Q=5 (l/min)
	bar (psi)	(psi/turn)	bar (psi)
20	60-210	63	200
20	(870-3000)	(914)	(2900)
	180-350	138	350
35	(2610-5000)	(2001)	(5000)

Pressure setting up to 410 bar: code on request.

Tamper resistant cap code ordering code 11.04.23.002
Mat. no. R930000752

Z


Preferred types

2

Туре	Material number
08410203022000B	R930003285
08410203023500C	R930054936
08410203092000A	R930003287

Туре	Material number
08410203093500B	R930003288

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics ® This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.