


Dual counterbalance, vented

RE 18307-70

Edition: 03.2016 Replaces: 08.2010

08.44.94 - X - Y - Z

A-VBSO-DE-CCAP-33




Description

It provides static and dynamic control of load by regulating the flow IN and OUT of the actuator, through ports C1 and C2. This valve module includes 2 sections, each one composed by a check and a relief valve pilot assisted by pressure in the opposite line: the check section allows free flow into the actuator, then holds the load against reverse movement; with pilot pressure applied at the line across, the pressure setting of the relief is reduced in proportion to the stated ratio until opening and allowing controlled reverse flow. The relief spring chambers are vented to air: relief and piloted opening are independent of back-pressure at V1 or V2.


Technical data

Max. operating pressure	410 bar (5945 psi)
Max. flow	150 l/min. (40 gpm)
Weight	4.9 kg (10.8 lbs)
Manifold material	Zinc plated steel
Fluid	Mineral oil (HL, HLP) according DIN 51524
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)
Viscosity range	5 to 800 mm ² /s (cSt)
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406
MTTFd	150 years see 18350-51
Other technical data	see data sheet 18350-50
Relief setting: at least 1.3 times the highest expected load.	


Note: for applications outside these parameters, please consult us.



Characteristic curve



2



Port sizes	V1 - V2	C1 - C2	
04	G 3/4	G 3/4	

	SPRINGS		
	Adj. pressure	Pres. increase	Std. setting
	range	bar/turn	Q=5 (I/min)
	bar (psi)	(psi/turn)	bar (psi)
35	150-350	110	350
33	(2175-5000)	(1595)	(5000)

Pressure setting up to 410 bar: code on request.


Tamper resistant cap code ordering code 11.04.30.001 Mat. no. R930005194

Preferred types

Туре	Material number	Туре
08449403043500B	R930008382	

Туре	Material number

Dimensions



^{*} The adjusting screw can be completely unscrewed. Do not exceed the indicated protrusion range of the adjusted screw.

Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5

P.O. Box no. 5

41015 Nonantola - Modena, Italy

Tel. +39 059 887 611 Fax +39 059 547 848

compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.