Rexroth Bosch Group


Dual counterbalance, vented

A-VBSO-DE-CCAP-78-FC2



Description

It provides static and dynamic control of load by regulating the flow IN and OUT of the actuator, through ports C1 and C2. This valve module includes 2 sections, each one composed by a check and a relief valve with balanced piston, pilot assisted by pressure in the opposite line: the check section allows free flow into the actuator, then holds the load against reverse movement; with pilot pressure applied at the line across, the pressure setting of the relief is reduced in proportion to the stated ratio until opening and allowing controlled reverse flow. Relief operates at the valve setting independent of back-pressure, but the piloted opening remains subject to additive pressure at V1 or V2. The relief spring chambers are vented to air: relief and piloted opening are independent of back-pressure at V1 or V2. For better safety and compact assembly, the C1 and C2 ports are gasket mounted directly on the actuator.



08.44.31 - X - Y - Z

RE 18308-64 Edition: 02.2019 Replaces: 03.2016


Technical data


350 bar (5000 psi)			
40 l/min. (11 gpm)			
1.8 kg (4 lbs)			
Zinc plated steel			
E0000000000014 (R930005947)			
Mineral oil (HL, HLP) according DIN 51524			
-30 °C to 100 (-22 to 212 °F)			
5 to 800 mm ² /s (cSt)			
Class 19/17/14 according to ISO 4406			
150 years see RE 18350-51			
see data sheet 18350-50			
Relief setting: at least 1.3 times the highest expected load.			

Note: for applications outside these parameters, please consult us.

¹⁾ Seals for 10 valves.

Characteristic curve






Preferred types

Туре	Material number	Туре	Material number
084431030235000	R930001974		

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.