


# Single counterbalance, relief compensated

RE 18307-48

Edition: 05.2017

Replaces: 03.2016


A-VBSO-SE-CC-30-PL



### Description

When pressure at V2 rises above the spring bias pressure, the check seat is pushed away from the piston and flow is allowed from V2 to C2. When load pressure at C2 rises above the pressure setting flow is relieved from C2 to V2. With pilot pressure at V1–C1, the pressure setting is reduced in proportion to the stated ratio of the valve, until opening and allowing flow from C2 to V2. The spring chamber is drained to V2. The valve applies a balanced piston design allowing relief operation at the valve setting independent of backpressure at V2. However, the piloted opening of the valve remains subject to additive pressure at port V2.

Note: port identified with M are not protected with calibrated orifice but in direct connection with pressure channels.




#### **Technical data**

08.45.17 - X - Y - Z

Max. operating pressure	410 bar (5945 psi)	
Max. flow	60 l/min. (16 gpm)	
Weight	see "Dimensions"	
Manifold material	Zinc plated steel	
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	5 to 800 mm <sup>2</sup> /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
MMTFd	150 years see data sheet 18350-51	
Other technical data	see data sheet 18350-50	
Relief setting: at least 1.3 times the highest expected load.		

Note: for applications outside these parameters, please consult us.

#### **Characteristic curve**



	ing code	08.4	5.17	X	Υ
_	counterbalance, compensated				
Pilot ra	atio				
03	4.2 : 1				

Port sizes	V1 - V2	C1 - C2	М
02	G 3/8	G 3/8	/
03	G 1/2	G 1/2	G 1/4

	SPRINGS		
Adj. pressure Pres. increase Sto		Std. setting	
	range	bar/turn	Q=5 (I/min)
	bar (psi)	(psi/turn)	bar (psi)
20	60-210	75	200
20	(870-3000)	(1088)	(2900)
35	100-350	165	350
	(1450-5000)	(2393)	(5000)

Pressure setting up to 410 bar: code on request.

Tamper resistant cap		
ordering code 11.04.23.003		
Mat. no.	R930000754	
Plug kit "M"		

Z


ordering code KP.04.08.002 Mat. no. R930005784

# **Preferred types**

Туре	Material number
08451703022000A	R930006858
08451703023500B	R930006857
08451703032000A	R930006921
08451703033500C	R930006922

Туре	Material number

#### **Dimensions**



## Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5

41015 Nonantola – Modena, Italy

Tel. +39 059 887 611 Fax +39 059 547 848

compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics

® This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.