Rexroth Bosch Group

Single counterbalance


A-VBSO-SE-78-PL-FC2



Description

When pressure at V2 rises above the spring bias pressure, the check seat is pushed away from the piston and flow is allowed from V2 to C2. When load pressure at C2 rises above the pressure setting, the direct operated relief function is activated and flow is relieved from C2 to V2. With pilot pressure at V1-C1, the pressure setting is reduced in proportion to the stated ratio of the valve, until opening and allowing flow from C2 to V2. The spring chamber is drained to V2, and back-pressure at V2 is additive to the pressure setting in all functions. For better safety and compact assembly, the C1 and C2 ports are gasket mounted directly on the actuator.

Note: port identified with M are not protected with calibrated orifice but in direct connection with pressure channels.



08.49.68 - X - Y - Z

RE 18307-36

Edition: 03.2016 Replaces: 07.2012


Technical data


Max. operating pressure	350 bar (5000 psi)	
Max. flow	40 l/min. (11 gpm)	
Weight	0.8 kg (1.76 lbs)	
Manifold material	Zinc plated steel	
Flange seal kit ¹⁾	E0000000000031 (R930005645)	
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	5 to 800 mm ² /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
Other technical data	see data sheet 18350-50	
Relief setting: at least 1.3 times the load induced pressure.		

Note: for applications outside these parameters, please consult us.

¹⁾ Seals for 5 valves.

Characteristic curve






Preferred types

Туре	Material number	Туре	Material number
084968030935000	R930003978		
		· · · · · · · · · · · · · · · · · · ·	

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.