


Single counterbalance

RE 18307-35

Edition: 11.2018

Replaces: 03.2016

A-VBSO-SE-78-PL



Description


When pressure at V2 rises above the spring bias pressure, the check seat is pushed away from the piston and flow is allowed from V2 to C2. When load pressure at C2 rises above the pressure setting, the direct operated relief function is activated and flow is relieved from C2 to V2. With pilot pressure at V1-C1, the pressure setting is reduced in proportion to the stated ratio of the valve, until opening and allowing flow from C2 to V2. The spring chamber is drained to V2, and back-pressure at V2 is additive to the pressure setting in all functions.

Technical data


08.49.85 - X - Y - Z

Max. operating pressure	350 bar (5000 psi)	
Max. flow	40 l/min. (11 gpm)	
Weight	0.76 kg (1.68 lbs)	
Manifold material	Zinc plated steel	
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	5 to 800 mm ² /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
MTTFD	150 years see RE 18350-51	
Other technical data	see data sheet 18350-50	
Relief setting: at least 1.3 times the load induced pressure.		


Note: for applications outside these parameters, please consult us.



Characteristic curve



A-VBSO-SE-78-PL | Single counterbalance



SPRINGS			
Adj. pressure	Pres. increase	Std. setting	
range	bar/turn	Q=5 (I/min)	
bar (psi)	(psi/turn)	bar (psi)	
200-350	175	350	
(2900-5000)	(2538)	(5000)	
	range bar (psi) 200-350	Adj. pressure Pres. increase range bar/turn psi) (psi/turn) 200-350 175	

Tamper resistant cap code ordering code 11.04.23.002
Mat. no. R930000752

Z


Preferred types

2

Туре	Material number
08498503093500A	R930004003

Туре	Material number

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5

41015 Nonantola – Modena, Italy

Tel. +39 059 887 611 Fax +39 059 547 848

compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics

® This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.