
# Flow divider, combiner

# A-DRF



# Description

This valve gives division of input flow from V to C1-C2, and re-combines flows in reverse direction from C1-C2 to V. The ratio between the flows through C1 and through C2 is maintained constant (typically 50% / 50%) over a wide range of pressure variations and of pressure imbalance in order to synchronize the motion of 2 actuators in both forward and reverse directions. In flow division mode, should either C1 or C2 be blocked, approximately 1÷2% of the available flow can be forced through the port still open.

OM.E1.21.90.02 - Z

Edition: 03.2016 Replaces: 04.2010


Rexroth

**Bosch Group** 


# **Technical data**

Max. operating pressure	350 bar (5000 psi)		
Flow division ratio: 50% - 50%			
For any chosen inlet flow capacity (refer to table Z), the slippage, or the difference from theoretical value between the divided flows, depends from the inlet flow, and is lowest in the top portion of the selected range: generally it never exceeds $\pm$ 3%.			
Weight	1.1 kg (2.4 lbs)		
Manifold material	Zinc plated steel		
Fluid	Mineral oil (HL, HLP) according DIN 51524		
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)		
Viscosity range	5 to 800 mm <sup>2</sup> /s (cSt)		
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406		
Other technical data	see data sheet 18350-50		

Note: for applications outside these parameters, please consult us.




#### **Characteristic curve**



RE 18309-59


## **Ordering code**



#### **Preferred types**

Туре	Material number	Туре	Material number
0ME12190020400C	R930056612		
0ME12190020800C	R930056614		
0ME12190021600C	R930056615		

## Dimensions



#### Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.