


Flow regulator 3 way, pressure compensated


VRFC3





Description

A constant flow rate, regardless of system pressures, is established from E to R, while a minimum pressure differential of appr. 5 bar (70 psi) exists between the two ports. Input flow supplied to E in excess of the regulated output at R is by-passed to T. Output flow can be varied from closed to the nominal maximum rating for the valve. Reverse flow from R to E is limited by the selected opening of the restrictor and is not pressure compensated. Flow from T to E or from T to R is not possible. Increasing or decreasing inlet flow may cause slight increase or decrease of Regulated flow.

Characteristic curve








Note: aluminium bodies are often strong enough for operating pressures exceeding 210 bar (3000 psi), depending from the

QE= max. inlet flow "E" port (see "Dimensions") QR= max. regulated flow "R" port (see "Dimensions")

	5111 01021
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)
Viscosity range	5 to 800 mm ² /s (cSt)
Recommended degree of fluid	Class 19/17/14 according to
contamination	ISO 4406
Other technical data	see data sheet 18350-50

Note: for applications outside these parameters, please consult us.



RE 18309-38

up to 210 bar (3000 psi)

0 - 3 turns

Aluminium

see "Dimensions"

Edition: 03.2016 Replaces: 04.2010

Technical data

Weight


Fluid

Operating pressure

Flow range adjustment

Manifold material

0M.32.03 - X - Y




Port sizes	E - R - T
02	G 3/8
03	G 1/2
04	G 3/4

Preferred types

Туре	Material number
0M3203700200000	R930004231
0M320370030000A	R930004232
0M3203700400000	R930004233
0M3203800200000	R930004241
0M320380030000A	R930004242
0M3203800400000	R930004244

Туре	Material number
0M3203400200000	R930004220
0M320340030000A	R930004221
0M3203400400000	R930004224

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.