


## 4/3 and 4/2 On-Off directional valve elements with LS (with Cross Piloted Counterbalance or Cross Piloted Check Valves Option)

RE 18301-23

Edition: 03.2022

EDG-DO...B1—EDG-DO...R1  
Component Series 1



- ▶ Size 6
- ▶ Series 1
- ▶ Maximum operating pressure:
  - ▶ 350 bar (5000 psi) on pump side
  - ▶ 350 bar (5000 psi) on consumer side
- ▶ Maximum flow at 6 bar (87 psi) 40 l/min (10.6 gpm)
- ▶ Ports connections G 3/8 - G 1/2 - SAE6 - SAE8
- ▶

**NEW spool position sensor available for this valve.**  
See RE18300-30

### General specifications

- ▶ The inlet section can be configured for either a fixed displacement pump or load-sense variable displacement pump. When simultaneous machine functions are actuated, the pre-compensators will automatically adjust to the highest load pressure via a shuttle arrangement, making the system circuit independent of variations in loads and pump pressures.
- ▶ - EDG-DO with Cross Piloted Counterbalance (B1) incorporates one or two Cross Piloted Counterbalance valves which allow free flow toward the A and B outlet ports, and lock in a leak free mode the flow returning from the actuator. Pilot pressure in the opposite line reduces the pressure setting of the counterbalance valve in proportion to the pilot ratio (4:1) until opening and allowing the flow return from the actuator. The pressure setting should be at least 1,3 times the highest expected load. Depending on the version selected, the counterbalance function can be double-acting or single-acting (only A ,only B or both A and B ports).
- ▶ - EDG-DO with Cross Piloted Check Valve (R1) incorporates one or two Cross Piloted Check Valves which allow free flow toward the A and B outlet ports, and lock in a leak free mode the flow returning from the actuator, until sufficient pilot pressure is built up in the opposite line and the check valve is opened.

### Main Field of Application

- ▶ ▶▶ Truck mounted applications
- ▶ ▶▶ Forestry machinery
- ▶ ▶▶ Forklifts and Telehandler
- ▶ ▶▶ Municipal vehicles
- ▶ ▶▶ Cranes
- ▶ ▶▶ Construction machines
- ▶ ▶▶ Aerial working platforms
- ▶ ▶▶ Heavy duty vehicles
- ▶ ▶▶ Agricultural machines
- ▶
- ▶

### Contents

Ordering details	2
Functional description	5
Technical data	6
Characteristic curves	7
External dimensions and fittings	8
External dimensions for spool with nominal flow 9	9
Electric connection	10

### New Series 1 features:

- Pole tube and coil (emproved corrosion resistance duration up to 500h)
- Label
- Flange with drain line for VMGLS and combination for EDG Electrohydraulic actuation
- Body valve zinc plating treatment for higher corrosion resistance protection up to 500h

## Ordering details

01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	
EDG	-	D	O	-	-	-	-	-	-	-	-	-	-	-	-	00	-	-	1

### Family

01	Directional Valve elements EDG Size 6	<b>EDG</b>
----	---------------------------------------	------------

### Type

02	Direct Acting	<b>D</b>
----	---------------	----------

### Configuration

03	On-Off	<b>O</b>
----	--------	----------

### Ports & Connections

04	G 3/8 DIN 3852	<b>G38</b>
	G 1/2 DIN 3852	<b>G12</b>
	9/16-18 UNF 2-B (SAE6)	<b>S06</b>
	3/4-16 UNF 2-B (SAE8)	<b>S08</b>
	Schäfer DN8-10-STH	<b>R08</b>

### Local compensator bias spring

05	4 bar (58 psi)	<b>1</b>
	6 bar (87 psi)	<b>2</b>

### Flange configuration

06	With P-Ta-Tb-LS-Ya-Yb-X-Y lines	<b>2</b>
	With P-Ta-Tb-LS-Ya-Yb-X-Y lines and LS return line	<b>3</b>

### Hydraulic connections in neutral

07	P, A, B closed and LS to T	<b>B</b>
	P closed and A, B, LS to T	<b>E</b>

### Spool variants

08	4/3 operated both sides A and B	<b>2</b>
	4/2 operated on side A only	<b>3</b>
	4/2 operated on side B only	<b>4</b>

### Notches dimension selection (from 1 to 9 according to table 1 and table 2)

09	Notch dimension selection P>A	-
10	Notch dimension selection P>B	-
11	Notch dimension selection (A>T)	- <sup>5)</sup>
12	Notch dimension selection (B>T)	- <sup>5)</sup>

### Voltage supply

13	Without coil	-	-	-	●	<b>00</b>
	12V DC	●	●	●	-	<b>0B</b>
	24V DC	●	●	●	-	<b>0C</b>
● = Available - = Not available						

### Electric connections

14	Without coils	<b>00</b>
	With coils, with connection DIN EN 175301-803	<b>01</b> <sup>1)</sup>
	With coils, with connection vertical Amp - Junior	<b>03</b>
	With coils, with connection horizontal DT04-2P	<b>07</b>

### Secondary valve types

15	Double or single counterbalance valve with 4:1 pilot ratio	<b>B1</b> <sup>2)3)</sup>
	Double or single piloted check valve with 4:1 pilot ratio and 0,5 bar cracking pressure	<b>R1</b> <sup>3)4)</sup>

### Secondary valve config. setting:

16	A>Ta	- <sup>2)</sup>
17	B>Tb	- <sup>4)</sup>

### Override option & Emergency Lever

18	Push pin type override	<b>00</b>
	Push button override on both sides A and B	<b>EP</b>
	Screw type override on both sides A and B	<b>EF</b>

### Component Series

19	Series 1	<b>1</b>
----	----------	----------

1) For mating connectors ordering code see data sheet RE 18325-90.

2) For B1 Selection Secondary valve types: see table 3.

3) Different pilot ratios available (8:1 and 12:1), please contact factory for further details

4) For R1 Selection Secondary valve types: see table 4

5) "I" for only meter in option.

## Ordering details

**Table 1**

Notches dimension selection --> Flow Rate	Local compensator bias spring	
	4bar	6bar
1 *	3 l/min	5 l/min
2 *	6 l/min	8 l/min
3 *	9 l/min	11 l/min
4 *	13 l/min	14 l/min
6 *	18 l/min	23 l/min
9 **	24 l/min	31 l/min
M **	-	40 l/min

\*Note: standard spool types (symmetrical):

1111 - 2222 - 3333 - 4444 - 6666 - 9999 - MMMM

\*\* Note: with 9 and M spool sizes delta pressure values exceed 30 bar (435 psi)

**Table 3**

Counterbalance valve configuration setting

9											
With valve cavity plugged (Normally closed plug)											
A	B	C	D	E	F	G	H	I	J	K	
50 bar	60 bar	70 bar	80 bar	90 bar	100 bar	110 bar	120 bar	130 bar	140 bar	150 bar	
725 psi	870 psi	1015 psi	1160 psi	1305 psi	1450 psi	1595 psi	1740 psi	1885 psi	2030 psi	2175 psi	
L	M	N	O	P	Q	R	S	T	U	V	X
160 bar	170 bar	180 bar	190 bar	200 bar	210 bar	220 bar	230 bar	240 bar	250 bar	270 bar	290 bar
2320 psi	2465 psi	2611 psi	2756 psi	2901 psi	3046 psi	3191 psi	3336 psi	3481 psi	3626 psi	3916 psi	4206 psi

**Note**

Pressure levels are set at 5 l/min (1.32 gpm).

For pressure higher than 290 bar (4206 psi), contact factory.

**Table 2**

Spool size selection guide							
P->A (corresponding A->T same size or "I" size)							
Notch size	1	2	3	4	6	9	M
P->B (corresponding B->T same size or "I" size)	1	X	X	●	●	●	●
	2	X	X	X	◇	●	●
	3	●	X	X	X	◇	●
	4	●	◇	X	X	X	◇
	6	●	●	◇	X	X	X
	9	●	●	●	◇	X	X
	M	●	●	●	●	◇	X

X = Standard spool flow rate configuration

◇ = Special spool flow rate configuration, contact factory



● = Not available

**Table 4**


R1 secondary valve types

A	9
0,5 bar (7.3 psi)	With valve cavity plugged


**Hydraulic layout**



**07 - Spool Variants**



## Functional description



- 1 Housing.
- 2 Main spool.
- 3 Return Spring.
- 4 Coil.
- 5 Ring nut.
- 6 LS shuttle valve.
- 7 Compensator spool.
- 8 VSO30 Check cartridge valve.
- 9 VSD30 Counterbalance cartridge valve.
- \* Normally open plug option as alternative to 8 or 9 cartridge selection.  
For Both ports A and B.

The EDG direct acting On-Off solenoid sectional valves with pressure compensation control the oil flow to actuators. These elements consist of a stackable housing (1) with a control spool (2), two solenoids (4), two return springs (3). Each solenoid (4), energized, displaces the control spool from its neutral-central position. When the spool is shifted, flow delivery starts and is controlled by a 2 way pressure compensator (7) ( $P > A$ ;  $P > B$ ). When the solenoid is de-energized, the return spring pushes the spool back in its neutral-central position. Each coil (4) is fastened to the solenoid tube by the ring nut (5). A push-pin manual override is included to actuate the valve without electrical power as needed.

### Load pressure compensation

The pressure compensator (7) keeps the pressure differential on the main spool (2). The flow to the consumers remains constant, despite varying loads. The highest load pressure on the pump is signaled via the LS line and the integrated shuttle valve (6). Port relief valves with anti-cavitation function on A and B (9) protect the system against pressure peaks and cavitation. LS relief valves (8), for each consumer port, can be adjusted according to specific application requirements.

## Technical data

General		
Valve element with 2 solenoids	kg (lbs)	2.2 (4.85)
Valve element with 1 solenoid	kg (lbs)	1.7 (3.75)
Ambient Temperature	°C (°F)	-30....+90 (-22....+194)
Hydraulic		
Maximum pressure at P, A and B ports	bar (psi)	350 (5000)
Maximum static pressure at T	bar (psi)	210 (3050) [in case of Emergency Lever option, max. pressure is limited up to 30 bar at T]
Max. regulated flow at 6 bar (87 psi)	l/min (gpm)	40 (10.6)
For E schemes symmetrical spool pattern in neutral position (connection A to T and B to T) E-schemes flow pattern with only meter IN (spool type E_ _ _ I I) in neutral position: the opening area is approx the 50% of nominal cross-section. This spool type is suitable in combination with load holding valves applications.		Approx. 2% of the nominal cross-section
Hydraulic fluid General properties: it must have physical lubricating and chemical properties suitable for use in hydraulic systems.		Mineral oil based hydraulic fluids HL (DIN 51524 part 1). Mineral oil based hydraulic fluids HLP (DIN 51524 part 2). For use of environmentally acceptable fluids (vegetable or polyglycol base) please consult us.
Fluid Temperature	°C (°F)	-30....+100 (-22....+212) (NBR seals)
Permissible degree of fluid contamination		ISO 4572: $\beta_{x \geq 75} X = 12 \dots 15$ ISO 4406: class 20/18/15 NAS 1638: class 9
Viscosity range	mm <sup>2</sup> /s	20....380 (optimal 30....46)
Electrical		
Voltage type		DC
Voltage tolerance (nominal voltage)	%	-10....+10
Duty		Continuous, with ambient temperature $\leq 50^\circ$ (122°F)
Coil wire temperature not to be exceeded	°C (°F)	180 (356)
Insulation class		H
Compliance with		Low Voltage Directive LVD 73/23/EC (2006/95/EC), 2004/108/EC
Coil weight	kg (lbs)	0.228 (0.503)
Voltage	V	12 24
Power consumption	W	20 20
Current (nominal at 20°C (68°F))	A	1.04 0.54
Resistance (nominal at 20°C (68°F))	$\Omega$	7.4 28.4


### Note

For applications with different specifications consult us

Code	Voltage [V]	Connector type	Coil description	Marking	Coil Mat no.
<b>=OB 01</b>	12 DC	EN 175301-803 (Ex. DIN 43650)	D3601 12DC	12 DC	R901393412
<b>=OB 03</b>	12 DC	AMP JUNIOR	D3603 12DC	12 DC	R901435507
<b>=OB 04</b>	12 DC	AMP JUNIOR Horizontal	D3604 12DC	12 DC	R901395031
<b>=OB 07</b>	12 DC	DEUTSCH DT 04-2P	D3607 12DC	12 DC	R901394397
<b>=OC 01</b>	24 DC	EN 175301-803 (Ex. DIN 43650)	D3601 24DC	24 DC	R901393577
<b>=OC 03</b>	24 DC	AMP JUNIOR	D3603 24DC	24 DC	R901435494
<b>=OC 04</b>	24 DC	AMP JUNIOR Horizontal	D3604 24DC	24 DC	R901395035
<b>=OC 07</b>	24 DC	DEUTSCH DT 04-2P	D3607 24DC	24 DC	R901394399


## Characteristic curves

### Performance limits




Measured with hydraulic fluid ISO-VG32 at 45° ±5 °C (113° ±9 °F); ambient temperature 20 °C (68 °F).

### Characteristic curve for EDG-DO...B1




Pressure drop	Curve no.
Fully piloted	1
Through check valve	2

### Characteristic curve for EDG-DO...R1



Cracking Pressure	Curve no.
0.5 bar (7.3 psi) free flow	1
Returning flow, fully piloted	2


External dimensions and fittings



- 1 Ring nut for coil locking ( $\varnothing$  30.3 mm).  
Torque 6 – 7 Nm (4.4 – 5.2 ft-lb).
- 2 Flange specifications. For tie rod and tightening torque information see data sheet RE 18301-90.
- 3 A and B ports.
- 4 Identification label.
- 5 Optional push-button manual override, EP type, for spool opening:  
it is pressure stuck to the ring nut for coil locking.  
Mat no. R930059524
- 6 Optional screw type manual override, EF type, for spool opening:  
it is screwed (torque 6-7 Nm (4.4-5.2 ft-lb)) to the tube as  
replacement of the coil ring nut. Mat no. R930059561.





**External dimensions for spool with nominal flow M**



- 1 Flow-boost system only for spool with nominal flow M. It always mounted on "a" side of the valve.

## Electric connection



### Bosch Rexroth Oil Control S.p.A.

Oleodinamica LC Division  
 Via Artigianale Sedrio, 12  
 42030 Vezzano sul Crostolo  
 Reggio Emilia - Italy  
 Tel. +39 0522 601 801  
 Fax +39 0522 606 226 / 601 802  
 compact-hydraulics-cdv@boschrexroth.com  
 www.boschrexroth.com/compacthydraulics

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.  
 Subject to change.