

1/2

Flow control valves Adjustable barrel type bidirectional restrictors



RE 18316-06/03.22

Performance



Description

SD Series

This line mounted valve provides a fully adjustable restriction. Pressure compensation is not provided and flow depends from pressure drop and oil viscosity. Once the flow is adjusted, lock the knurled ring nut (H) in order to maintain the desired opening.

Minor leakage in both directions can be expected with valve fully closed.

With valve fully closed, max admitted pressure: 250 bar.

psi bar A-B B-A 45-3. 10**/**11 2.5 36 PRESSURE - ∆ p 2 27 1.5 18 9 0.5 0 l/min 0 25 ò 50 75 1Ò0 125 150 gpm 0 40 10 20 30 FLOW - Q Throttle fully open

Advantages

-Compact design and inline mounting for space saving. -Seven sizes provide great adaptability to the system. -Easiness of adjustment.

-Mounting position is unrestricted.

Technical data

Code	Pressure P max bar (psi)	Flow Q max I/min (gpm)	Weight kg (lbs)
SD 7	350 (5000)	12 (3)	0.29 (0.64)
SD 10	350 (5000)	30 (8)	0.39 (0.86)
SD 13	350 (5000)	45 (12)	0.69 (1.52)
SD 19	250 (3600)	80 (21)	1.08 (2.38)
SD 25	250 (3600)	140 (37)	3.0 (6.6)

Steel body, zinc plated

Dimensions



Ports size / Dimensions

Code	Ports size A-B	Ø D mm (inches)	L mm (inches)	K mm (inches)
SD 7	G 1/4	35 (1.38)	62 (2.44)	5 (0.20)
SD 10	G 3/8	38 (1.50)	72 (2.84)	7 (0.28)
SD 13	G 1/2	48 (1.89)	86 (3.39)	8 (0.32)
SD 19	G 3/4	55 (2.17)	100 (3.94)	11 (0.43)
SD 25	G 1	79 (3.11)	126 (4.96)	12 (0.47)

Applications

The SD Series valve is a fully and easily adjustable non-compensated flow control which can be employed for meter-in (Port A connected to the actuator inlet) or meter-out (Port B connected to the actuator outlet in order to control the oil flow from the actuator). The cost effectiveness and the easiness of adjustment make it suitable for many circuits and many applications where a non-compensated flow control is desired.

Ordering code

	SD	
series 7	= 7	
series 10	= 10	
series 13	= 13	
series 19	= 19	
series 25	= 25	

Type	Material number	Туре	Material number	Туре	Material number
SD 7	R932500579				
SD 10	R932500580				
SD 13	R932500581				
SD 19	R932500582				
SD 25	R932500583				

Bosch Rexroth Oil Control S.p.A. Fimma Division (Rge 2) Via G. Bovio, 7 Z.l. Mancasale 42124 Reggio Emilia, Italy Tel. +39 0522 517 277 Fax +39 0522 517 125 cartridges@oilcontrol.com www.boschrexroth.com © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Subject to change.