

Sandwich valve module with solenoid valve and flow restrictor

EM-VEI-16-08A-ST-CETOP 3-B1


OP.62 - K - X - 29 - Y - Z

RE 18332-88


Edition: 04.2023

Replaces: 12.2016

Dimensions



Configurations available (K)



[mm (inches)]

Technical data

Max. flow: up to 40 l/min (11 gpm)


Max. operating pressure: 210 bar (3000 psi)

Standard manifold in high strength aluminium.

For working pressure up to 350 bar (5000 psi) and for fatigue applications with any working pressure, steel manifolds are available upon request.


Fluids: Mineral-based or synthetics with lubricating properties at viscosities of 20 to 380 mm²/s (cSt)

Other technical data See data sheet 18350-50

Flow restrictor ST-C-06 (see data sheet 18321-26)

Cavity: CA-08A-2N

X	ST-C-06 ADJUSTMENTS	
03	Leakproof hex. socket screw	
04	Handknob and locknut	

Solenoid cartridge valve VEI-16-08A
(see data sheets 18323-25 and 18323-26)**Manual override options (Y)**


Seal and prot. cap. (Z)	A	B	C	D	E	F
	O	K=05 K=06	K=06	K=06	K=05	K=05
	V	K=05 K=06	K=06	K=06	K=05	K=05
	P	/	K=06	K=06	K=05	/
	T	/	K=06	K=06	K=05	/

Technical data


General	
Installation orientation	Unrestricted
Ambient temperature range	-30 to 90 °C (-22 to 194 °F)
Hydraulic	
Max. operating pressure	350 bar (5000 psi)
Flow range	0.5 - 40 l/min (0.1 - 11 gpm)
Max. internal leakage	5 drops/min.
Switching time	Opening ≤ 50 ms Closing ≤ 100 ms
Fluid temperature range	-20 to 80 °C (-4 to 176 °F)
Fluids: Mineral-based or synthetics with lubricating properties at viscosities of 20 to 380 mm ² /s (cSt)	
Installation torque	39 - 51 Nm (29 - 38 ft-lbs)
Recommended degree of fluid contamination	Nominal value max. 10 µm (NAS 8) ISO 4406 19/17/14
MTTFd	150 years (see 18350-51)
Cavity	CA-08A-2N (see 18325-70)
Other technical data	See data sheet 18350-50
Electrical	
Type of voltage	DC voltage
Coil type	D36
Supply voltage	See data sheet 18325-90
Voltage tolerance against ambient temperature	See characteristic curve
Power consumption	20 W
Type of protection	See data sheet 18325-90
Note: Coils must be ordered separately	

Characteristic curves


ST-C-06



VEI-16-08A all Versions - Admissible supply voltage Vs. Ambient temperature at 100% duty cycle



VEI-16-08A all Versions



Ordering code

OP.62		K	X	29	Y	Z
Sandwich valve module with solenoid valve and flow restrictor		05				
Configuration		06				
Configuration						
See page 1						
Flow restrictor adjustments see page 2						