

Pilot operated check, pilot to open SUN cavity interchange, T-2A

VSON-12U



Description

When pressure at 2 rises above the spring bias pressure, the poppet is pushed from its seat and flow is allowed from 2 to 1. The valve is normally closed (checked) from 1 to 2. When sufficient pilot pressure is present at port 3, the pilot piston acts to push the poppet from its seat and flow is allowed from 1 to 2. Precision machining and hardening processes allow virtually leak-free performance in the checked condition. In case of valve application in redundancy systems it is especially recommended to use version with sealed pilot piston.

04.33.07 - X - 86 - Z

RE 18319-40

Edition: 09.2019 Replaces: 01.2019

Technical data		
Technical data		
Max. operating pressure	350 bar (5000 psi)	
Max. flow	120 l/min. (32 gpm)	
Pilot ratio	3.2:1	
Max. internal leakage	5 drops/min.	
Fluid temperature range	-30 to 100 °C (-22 to 212 °F)	
Installation torque	60 - 70 Nm (44 - 52 ft-lbs)	
Weight	0.25 kg (0.55 lbs)	
Cavity	SUN T-2A	
Lines bodies and standard	Please refer to section "Hydraulic	
assemblies	integrated circuit" or consult factory	
Seal kit ¹⁾	Code: RG12U9020110100	
	material no: R930005599	
Fluids	Mineral-based or synthetics with	
	lubricating properties	
	at viscosities of 5 to 800 mm ² /s (cSt)	
Recommended degree of	Nominal value max. 10µm (NAS 8) /	
fluid contamination	ISO 4406 20/18/15	
Installation position	No restrictions	
Other Technical Data	See data sheet 18350-50	

1) Only external seals for 10 valves





Characteristic curve





Preferred types

Туре	Material number	Туре	Material number
04330700860000A	R901106638	043307008605000	R930054250
04330710860000A	R901106639	043307108605000	R930054274

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.