

RE 18316-01/10.22 1/2 Replaces: 10.09

Flow control valves

Fixed orifice restrictor with reverse flow check



VF-MF

04.46.03.00-Y-Z





Description

The "B-A" flow is restricted by a calibrated orifice, while flow "A-B" is always allowed through the incorporated check valve. Pressure compensation is not provided and flow depends from pressure drop and oil viscosity.

drop and oil viscosity. The valve is assembled with two hexagonal threaded sleeves and an internal check poppet. The drawing shows the valve with Male port A and Female port B: the two sleeves can be assembled in the reversed order and the result will be Female A port and Male B port.

Technical data

Port	Pressure P max bar (psi)	Flow Q max l/min (gpm)	Weight kg (lbs)
G	350	10 (3)	0.10
1/4	(5000)		(0.22)

Steel body, zinc plated.

Installation torque: 33 - 37 Nm (24 - 27 ft-lb)

Advantages

-Very compact design and inline mounting for space saving. -Mounting position is unrestricted.

MTTFD: 150 years see RE18350-51



Y	Ports A-B	L mm (inches)	ا mm (inches)	Hex mm (inches)	
09	G 1/4	52 (2.05)	10.5 (0.41)	19 (0.75)	

The valve is only available with G ¼ ports, with different size restriction orifices, as indicated by the table of orifices.

Calibrated orifices											
Z	09	06	00	07	10	12	11	03	08	05	01
Calibrated orifice Ø mm (inches)	0.3* (0.012*)	0.4 (0.016)	0.5 (0.020)	0.6 (0.024)	0.7 (0.028)	0.8 (0.032)	0.9 (0.035)	1.0 (0.039)	1.3 (0.051)	1.5 (0.059)	1.75 (0.069)
* Hole Ø 0.5 mm (0.020 inch.) with Ø 0.4 mm (0.016 inch.) wire.											

Applications

In a variety of cases when a one-way restrictor is needed, especially for cushioning a control circuit (like servo-controls), or delaying brake engagement, etc.

-Control of delay for brake disengagement.

-Dampening of pressure peaks in joystick controlled lines.

-Simple and cost-effective solution for a one-way flow control.

Ordering code



Туре	Material number	Туре	Material number	Туре	Material number
04460300090000A	R930000645	044603000912000	R930000655		
04460300090100A	R930000646				
04460300090300A	R930000647				
04460300090500A	R930000648				
04460300090600A	R930000649				
04460300090700A	R930000650				
04460300090800A	R930000651				
04460300090900A	R930000652				
04460300091000A	R930000653				
044603000911000	R930000654				

Bosch Rexroth Oil Control S.p.A. Fimma Division (Rge 2) Via G. Bovio, 7 Z.I. Mancasale 42124 Reggio Emilia, Italy Tel. +39 0522 517 277 Fax +39 0522 517 125 cartridges@oilcontrol.com www.boschrexroth.com © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.