

# Sequence, pilot operated spool type, compensated

## VSQP-CC-150



### Description

Initially, the flow goes to a side line connected to V1, not shown here, and energizes a first actuator until pressure increases to meet the selected valve setting; then flow opens the relief cartridge and passes from V1 to C1 energizing the second actuator connected to C1. The valve applies a balanced relief piston allowing relief operation at the valve setting independent of back-pressure at C1. With line pressure equal or higher than setting, after valve opening, the full pressure is transferred from V1 to C1 and to the second actuator. The check valve allows reverse flow, from C1 to V1. 05.24.06 - X - Y - Z

RE 18309-88

Edition: 03.2016 Replaces: 04.2010

#### Technical data

Operating pressure	up to 210 bar (3000 psi)		
Max. flow	150 l/min. (40 gpm)		
Leakage: 100 cc/min. (6 in <sup>3</sup> /min.) at max. relief setting			
For a good performance, the pressure in the secondary circuit should not drop below 20 bar (290 psi).			
Weight	1.1 kg (2.4 lbs)		
Manifold material	Aluminium		
Note: aluminium bodies are often strong enough for operating			
pressures exceeding 210 bar (3000 psi), depending from the			
fatigue life expected in the specific application. If in doubt, consult			
our Service Network.			
Fluid	Mineral oil (HL, HLP) according		
	DIN 51524		
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)		
Viscosity range	10 to 500 mm <sup>2</sup> /s (cSt)		
Recommended degree of fluid	Class 19/17/14 according to		
contamination	ISO 4406		

Note: for applications outside these parameters, please consult us.

see data sheet 18350-50



#### **Characteristic curve**

Other technical data





#### **Preferred types**

Туре М	Naterial number	Туре	Material number
052406030320000 R	930001501		
052406030420000 R	3930001503		
052406030420000 R	8930001503		

#### Dimensions



#### Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.