

Pilot operated check, dual

VSO-DE



Description

Flow is allowed to pass in one direction (V1 to C1 or V2 to C2), then the valve remains closed (checked) in both reverse directions (C1 to V1 or C2 to V2) in order to hold and lock in position the cylinder or other actuators; reverse flow is possible only when sufficient pilot pressure is applied at V2 or V1, which act as cross connected pilot ports, and the pilot piston lifts the poppet from its seat overcoming cylinder port pressure.

In case of valve application in redundancy systems it is especially recommended to use version with sealed pilot piston. 05.53.01 - X - 04 - Z

RE 18307-18

Edition: 09.2019 Replaces: 03.2016

Technical data

Operating pressure	up to 210 bar (3000 psi)		
Max. flow	100 l/min. (26 gpm)		
Pilot ratio	4:1		
Weight	2.6 kg (5.7 lbs)		
Manifold material	Aluminium		
Note: aluminium bodies are often strong enough for operating pressures exceeding 210 bar (3000 psi), depending from the fatigue life expected in the specific application. If in doubt, consult our Service Network.			

Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	10 to 500 mm ² /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
Other technical data	see data sheet 18350-50	
The version with O-Ring and heavier spring is generally recommended.		

Note: for applications outside these parameters, please consult us.



Characteristic curve



Ordering code



		SPRINGS	
		Cracking pressure bar (psi)	
00	only for X=00	1.5 (22)	
01	only for X=00 and X=10	8 (116)	

04	G 3/4	G 3/4	

Preferred types

Туре	Material number	Туре	Material number
055301000400000	R930002396	055301100401000	R930002403
055301000401000	R930002397		

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.