

Directional poppet type, shuttle

Common cavity, Size 10


SELB-10A

04.94.09.00.85.00

RE 18319-79

Edition: 03.2016

Replaces: 08.2015




Technical data

Max. operating pressure	220 bar (3190 psi)
Max. flow	See performance graph
Max. internal leakage	15 drops/min.
Fluid temperature range	-30 to 100 °C (-22 to 212 °F)
Installation torque	41 - 47 Nm (30 - 35 ft-lbs)
Weight	0.4 kg (0.88 lbs)
Common cavity	CA-10A-3N (see data sheet 18325-70)
Line bodies and standard assemblies	Please refer to section "Hydraulic integrated circuit" or consult factory
Seal kit ¹⁾	Code: RG10A3010520100 material no: R901111369
Fluids	Mineral-based or synthetics with lubricating properties at viscosities of 5 to 800 mm ² /s (cSt)
Recommended degree of fluid contamination	Nominal value max. 10µm (NAS 8) / ISO 4406 19/17/14
Installation position	No restrictions
Other Technical Data	See data sheet 18350-50


Description

The single ball shuttle allows flow from the higher pressure of two work ports 1 and 3 to the 2 port.

1) Only external seals for 10 valves



Characteristic curve



Ordering code

04.94.09.00	85	00	00	*
--------------------	-----------	-----------	-----------	----------

Directional poppet type, shuttle

Common cavity, Size 10

Series 0/A to L
unchanged performances and dimensions


Version and options standard

Preferred types

Type	Material number
04940900850000A	R930056708

Type	Material number

Dimensions



Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5
P.O. Box no. 5
41015 Nonantola – Modena, Italy
Tel. +39 059 887 611
Fax +39 059 547 848
compact-hydraulics-cv@boschrexroth.com
www.boschrexroth.com/compacthydraulics

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.