

# Flow regulator 3 way, pressure compensated

## VRFC3



### Description

A constant flow rate, regardless of system pressures, is established from E to R, while a minimum pressure differential of appr. 5 bar (70 psi) exists between the two ports. Input flow supplied to E in excess of the regulated output at R is by-passed to T. Output flow can be varied from closed to the nominal maximum rating for the valve. Reverse flow from R to E is limited by the selected opening of the restrictor and is not pressure compensated. Flow from T to E or from T to R is not possible. Increasing or decreasing inlet flow may cause slight increase or decrease of Regulated flow.

#### RE 18309-37

Edition: 03.2016 Replaces: 04.2010

### Technical data

OM.32.03 - X - 97

| Operating pressure  | up to 210 bar (3000 psi)                     |  |  |
|---|--|--|--|
| QE= max. inlet flow "E" port 40 l/min. (11 gpm)   |  |  |  |
| QR= max. regulated flow "R" port 25 l/min. (7 gpm)  |  |  |  |
| Flow range adjustment   | 0 - 3 turns                                  |  |  |
| Weight  | 0.55 kg (1.21 lbs)                           |  |  |
| Manifold material   | Aluminium                                    |  |  |
| Note: aluminium bodies are often strong enough for operating<br>pressures exceeding 210 bar (3000 psi), depending from the<br>fatigue life expected in the specific application. If in doubt, consult<br>our Service Network. |  |  |  |
| Fluid   | Mineral oil (HL, HLP) according<br>DIN 51524 |  |  |
| Fluid temperature range   | -30 °C to 100 (-22 to 212 °F)                |  |  |
| Viscosity range   | 5 to 800 mm <sup>2</sup> /s (cSt)            |  |  |
| Recommended degree of fluid   | Class 19/17/14 according to                  |  |  |

Note: for applications outside these parameters, please consult us.

ISO 4406

see data sheet 18350-50



#### **Characteristic curve**

contamination

Other technical data







#### Preferred types

| Туре            | Material number | Туре | Material number |  |  |
|-----------------|-----------------|------|-----------------|--|--|
| 0M3203709700000 | R930004239      |      |                 |  |  |
| 0M3203809700000 | R930004246      |      |                 |  |  |
| 0M3203409700000 | R930004226      |      |                 |  |  |

#### Dimensions



#### Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.