## Rexroth Bosch Group

# Single counterbalance, relief compensated

### VBSO-SE-CC



#### Description

When pressure at V2 rises above the spring bias pressure, the check valve poppet is pushed away from the piston and flow is allowed from V2 to C2. When load pressure at C2 rises above the pressure setting, the relief function is activated and flow is relieved from C2 to V2. With pilot pressure at V1–C1, the pressure setting is reduced in proportion to the pilot ratio, until opening and allowing flow from C2 to V2. The spring chamber is drained to V2. The valve applies a balanced piston allowing relief operation at the valve setting independent of back-pressure at V2. However, the piloted opening of the valve remains subject to additive pressure at port V2.



## 05.41.06 - X - Y - Z

**RE 18307-51** Edition: 03.2016 Replaces: 04.2010

#### **Technical data**

Operating pressure	up to 210 bar (3000 psi)	
Max. flow	see performance graph	
Weight	see "Dimensions"	
Manifold material	Aluminium	
Note: aluminium bodies are often pressures exceeding 210 bar (30 fatigue life expected in the specif our Service Network.		
Fluid	Mineral oil (HL, HLP) according DIN 51524	
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)	
Viscosity range	5 to 800 mm <sup>2</sup> /s (cSt)	
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406	
Other technical data	see data sheet 18350-50	
Relief setting: at least 1.3 times the	e highest expected load.	

Note: for applications outside these parameters, please consult us.

#### **Characteristic curve**





	SPRINGS		
	Adj. pressure	Pres. increase	Std. setting
	range	bar/turn	Q=5 (l/min)
	bar (psi)	(psi/turn)	bar (psi)
20	60-210	54	200
	(870-3000)	(783)	(2900)
25	100-350	95	350
35	(1450-5000)	(1378)	(5000)

Tamper resistant cap codeordering code 03.05.01.001Mat. no.R930000470

Ζ

#### Preferred types

G 3/4

04

Туре	Material number
054106020320000	R930001670
05410602033500A	R930001671
054106020420000	R930001674
05410602043500A	R930001675
054106100320000	R930001678

G 3/4

Туре	Material number
05410610033500A	R930001680
054106100420000	R930001941
054106100435000	R930001687

#### Dimensions



#### Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.