

1/4 **RE 18324-04/11.19** Replaces: RE 18324-04/01.16

Solenoid operated valves direct acting poppet 2-way double lock





OD.11 - X - 40 - Y - 00



\mathbf{r}	~	n	\sim	r 0	
G	e	[]	e	l d	i L

VEDT-08F-A-16

General		
Weight	kg (lbs)	0.22 (0.48)
Installation orientation		Optional
Ambient temperature range	°C (°F)	-30 to 60 (-22 to 140)

Hydraulic

Ilyulautic		
Max. operating pressure bar (ps		250 (3600)
Max. flow l/min. (gpm)		25 (7)
Max. internal leakage	drops/ min.	20
Fluid temperature range	°C (°F)	-20 to 80 (-4 to 176)
Response time	ms.	40-60 at nominal flow (oil at 46 cSt)
Fluids		Mineral-based or synthetics with lubricating properties at viscosities of 20 to 380 mm ² /s (cSt)
Installation torque	Nm (ft-lbs)	
Recommended degree of fluid contamination		Nominal value max. 10µm (NAS 8) ISO 4406 19/17/14
Special cavity		Hydac 06020
Lines bodies and standard assemblies		Please refer to section "Hydaulic integrated circuit" or consult factory
Seal kit		RG40E201053010 R934003587
Seal kit coil		RG16A1PMVQ0010 R934003962
Other technical data		See data sheet RE 18350-50

Etootiilout		
Type of voltage	DC voltage	
Coil type	S7	
Supply voltage	See data sheet RE 18325-90	
Power	30	
consumption	130	
Duty cycle coil %	See performance graphs	
Type of protection	See data sheet RE 18325-90	
Nominal voltage coil 30W	/ -10% +10%	
Note: Coils must be ordered congrately		

Note: Coils must be ordered separately.

Dimensions

Solenoid operated valves poppet 2-way double lock - Special cavity



push style manual override

3/4

Performance graphs

Performance limits

(Hot coil at nominal voltage)

version 31 (NC)











Ordering code



Special cavity: CA-08F-2N

Туре	Material number
OD1131406A0000	R934003630
OD1131406B0000	R934003631
OD1132406A0000	R934003628
OD1132406B0000	R934003629

Туре	Material number

Bosch Rexroth Oil Control S.p.A. Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.