## Rexroth Bosch Group

# Single counterbalance, vented

## A-VBSO-SE-CCAP-33-PL-FC1



## Description

When pressure at V2 rises above the spring bias pressure, the check seat is pushed away from the piston and flow is allowed from V2 to C2. When load pressure at C2 rises above the pressure setting, the relief function is activated and flow is relieved from C2 to V2. With pilot pressure at V1–C1, the pressure setting is reduced in proportion to the pilot ratio, until opening and allowing flow from C2 to V2. The spring chamber is vented to atmosphere allowing operation of all functions independent of back-pressure at V2. For better safety and compact assembly, the C2 port is gasket mounted directly on the actuator.

**Note:** port identified with M are not protected with calibrated orifice but in direct connection with pressure channels.



## 08.45.88 - X - Y - Z

**RE 18307-53** Edition: 03.2016 Replaces: 03.2014

### **Technical data**

Max. operating pressure	410 bar (5945 psi)		
Max. flow	150 l/min. (40 gpm)		
Weight	see "Dimensions"		
Manifold material	Zinc plated steel		
Flange seal kit <sup>1)</sup>	E0000000000057 (R930060587)		
Fluid	Mineral oil (HL, HLP) according DIN 51524		
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)		
Viscosity range	5 to 800 mm <sup>2</sup> /s (cSt)		
Recommended degree of fluid contamination	Class 19/17/14 according to ISO 4406		
MTTFd	150 years see 18350-51		
Other technical data	see data sheet 18350-50		
Relief setting: at least 1.3 times the highest expected load.			
The pilot line includes adjustable hydraulic damping, for fine tuning of stability and response.			

Note: for applications outside these parameters, please consult us.

<sup>1)</sup> Seals for 10 valves.







Ø 12 (0.47)

G 1/4

			SPRINGS	
		Adj. pressure	Pres. increase	Std. setting
		range	bar/turn	Q=5 (l/min)
		bar (psi)	(psi/turn)	bar (psi)
35	for	150-350	110	350
	X=13	(2200-5000)	(1595)	(5000)
	for	150-350	84	350
	X=15	(2200-5000)	(1218)	(5000)

Pressure setting up to 410 bar: code on request.

Tamper resistant cap code				
ordering code	11.04.30.001			
Mat. no.	R930005194			

#### Preferred types

G 3/4

04

Туре	Material number	Туре	Material number
08458813033500E	R930008378	08458815033500D	R930050624
08458813043500D	R930050622	08458815043500D	R930008411

#### Dimensions



\* The adjusting screw can be completely unscrewed. Do not exceed the indicated protrusion range of the adjusted screw.

Bosch Rexroth Oil Control S.p.A. Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.