

RE 18330-05/04.23

Replaces: RE 18330-05/07.12

Relief, pilot operated poppet type


Common cavity

Cartridge style in manifold

VSPC-10A-C

OR.05 - K - X - Y - Z - W

Dimensions



Technical data

Max flow:	up to 80 l/min	(21 gpm)
Max operating pressure for steel body:	350 bar	(5000 psi)
Max operating pressure for aluminium body:	210 bar	(3000 psi)

To order only manifold see data sheet RE 18325-85





Table “Y”

[illegible]

Cartridge style



SIZE 10

Table “K”

			K				
CARTRIDGE CODE	04	12	09	X	85	Z	VSPC-10A

Table “X”

X	ADJUSTMENTS		OPTIONS
03	Leakproof hex. socket screw		
04	Handknob and locknut		
			Ordering code 11.04.23.002

CARTRIDGE TECHNICAL DATA


Common cavity: **CA-10A-2N**

For other details see data sheet RE 18318-11

Table “Z”

[illegible]

Performance graph



Ordering code

OR.05	K	X	Y	Z	W
-------	---	---	---	---	---

Manifold with relief pilot operated poppet type

Cartridge style - Common cavity
(see table K on page 2)

Cartridge style - Adjustments
(see table X on page 2)

Manifold material

= 00	Aluminium manifold
------	--------------------

= S0	Steel manifold
-------------	----------------

Settings - Springs
(see table Z on page 2)

Manifold style - Dimensions and port sizes
(see table Y on page 1)

Preferred types (readily available)

[illegible][illegible]

Further types available by request