

Relief, direct acting poppet type differential area


Common cavity

Cartridge style in manifold

VSDN-08A-C

OR.12 - K - X - Y - Z - W

Dimensions



Technical data

Max flow:	up to 50 l/min	(13 gpm)
Max operating pressure for steel body:	350 bar	(5000 psi)
Max operating pressure for aluminium body:	210 bar	(3000 psi)

To order only manifold see data sheet RE 18325-85




Table “Y”

[illegible]

Cartridge style




Table “K”

			K				
CARTRIDGE CODE	04	15	22	X	56	Z	VSDN-08A

Table “X”

X	ADJUSTMENTS		OPTIONS
03	Leakproof hex. socket screw		
			Ordering code 11.04.23.002


CARTRIDGE TECHNICAL DATA

Common cavity: **CA-08A-2N**
For other details see data sheet RE 18318-02

Table “Z”

[illegible]

Performance graphs



Ordering code

OR.12	K	X	Y	Z	W
-------	---	---	---	---	---

Manifold with relief direct acting poppet type differential area

Cartridge style - Common cavity
(see table K on page 2)

Cartridge style - Adjustments
(see table X on page 2)

Manifold material

= 00	Aluminium manifold
= S0	Steel manifold

Settings - Springs
(see table Z on page 2)

Manifold style - Dimensions and port sizes
(see table Y on page 1)

Preferred types (readily available)

Type	Material number	Type	Material number
OR1222030210S0	R934003525		
OR1222030220S0	R934003526		
OR1222030235S0	R934003527		

Further types available by request