

Flow regulator 3 way, combination type pressure compensated

VRFC3C



Description

A constant priority flow, regardless of system pressures, is established from E to P, while a minimum pressure differential of appr. 5 bar (70 psi) exists between the two ports. While the regulated priority flow from P is used in the priority circuit, the flow supplied to E in excess of priority is by-passed to B port and can be sent to power other actuators. Priority flow can be varied from closed to the nominal maximum rating of the valve. Reverse flow from P to E is limited by the selected opening of the restrictor and is not pressure compensated. Reverse flow from B is not permitted.

Characteristic curve



0M.42.03 - X - Y

RE 18309-50

Edition: 03.2016 Replaces: 04.2010

Technical data

contamination

Other technical data

Operating pressure	up to 210 bar (3000 psi)						
QE= max. inlet flow "E" port (see	"Dimensions")						
QP= max. priority flow "P" port (see "Dimensions"						
Flow range adjustment	0 - 3 turns						
Weight	see "Dimensions"						
Manifold material	Aluminium						
Note: aluminium bodies are often strong enough for operating pressures exceeding 210 bar (3000 psi), depending from the fatigue life expected in the specific application. If in doubt, consult our Service Network.							
Fluid	Mineral oil (HL, HLP) according DIN 51524						
Fluid temperature range	-30 °C to 100 (-22 to 212 °F)						
Viscosity range	5 to 800 mm ² /s (cSt)						
Recommended degree of fluid	Class 19/17/14 according to						

Note: for applications outside these parameters, please consult us.

ISO 4406

see data sheet 18350-50





Port sizes	E - B - P						
02	G 3/8						
03	G 1/2 G 3/4 G 1						
04							
05							

Preferred types

Туре	Material number
0M4203700200000	R930004324
0M4203700300000	R930004325
0M4203700400000	R930004328
0M4203700500000	R930004329
0M4203800200000	R930004332
0M4203800300000	R930004333

Туре	Material number
0M4203800400000	R930004334
0M4203800500000	R930004336
0M4203400200000	R930004317
0M4203400300000	R930004318
0M4203400400000	R930004319
0M4203400500000	R930004320

Dimensions



70	130	10	56.5	48	122.5	150	6	54	65	120	40	130	8.5	190 l/min	380 l/min	G1	4.4
(2.76)	(5.12)	(0.39)	(2.22)	(1.89)	(4.82)	(5.91)	(0.24)	(2.13)	(2.56)	(4.72)	(1.58)	(5.12)	(0.34)	50 gpm	100 gpm		(9.7)
50	135	10	44	54	130	155	6	35	55	83	40	90	8.5	90 I/min 24 gpm	150 I/min	C 2/4	2.5
(1.97)	(5.32)	(0.39)	(1.73)	(2.13)	(5.12)	(6.1)	(0.24)	(1.38)	(2.17)	(3.27)	(1.58)	(3.54)					
40	110	10	37	45	108	130	6	38	42	64	40	70	6.5	55 l/min	90 l/min	C 1/2	1.3
(1.58)	(4.33)	(0.39)	(1.46)	(1.77)	(4.25)	(5.12)	(0.24)	(1.5)	(1.65)	(2.52)	(1.58)	(2.76)	(0.26)	15 gpm	24 gpm	GIZ	(2.87)
40	110	10	37	45	108	130	6	38	42	64	40	70	6.5	30 l/min	55 l/min	G 3/8	1.3
(1.58)	(4.33)	(0.39)	(1.46)	(1.77)	(4.25)	(5.12)	(0.24)	(1.5)	(1.65)	(2.52)	(1.58)	(2.76)	(0.26)	8 gpm	15 gpm	0 3/0	(2.87)
s	L5	L4	L3	L2	L1	1	14	1	H3	H2	H1	Н	E	QP	QE	v	Weight
3	LO	L4	LJ		LI	L			пэ	пг	пі	п	Г	QF	QE	T	kg (lbs)

Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola – Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-pib@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.