

RE 18329-75/01.19 1/2 Replaces: RE 18329-75/03.16

Insert type Flow control, 2-way pressure compensated fixed setting



SFC1







0T.F1.01.00 - Y - Z

Description

A constant flow rate, regardless of system pressures, is established from 1 to 2 while a minimum pressure differential of 145 psi exists between the two ports. The valve cannot be adjusted for variable flow output. Flow from 2 to 1 is limited by the diameter of the selected control orifice and is not pressure compensated.

Technical data

Max. operating pressure	bar (psi)	210 (3000)				
Max. flow I/m	in. (gpm)	see "Regulated flow range" table				
Fluid temperature range	°C (°F)	-30 to 100 (-22 to 212)				
Weight	kg (lbs)	see "Dimensions" table				
Special cavity		see "Dimensions"				
Lines bodies and standa assemblies	rd	Please refer to section "Hydraulic integrated circuit" or consult factory				
Fluids		Mineral-based or synthetics with lubricating properties at viscosities of 10 to 500 mm ² /s (cSt)				
Recommended degree o contamination	f fluid	Nominal value max. 10µm (NAS 8 ISO 4406 20/18/15				
Installation		No restrictions				
Other Technical Data		See data sheet RE 18350-50				



Dimensions G ØF H1. (2)മ Ŧ $\bigcirc \bigcirc$ Hmin ပ Ŧ Δ Ø E min Ø mm (Inches) G

G *	А	В	С	D	E	F	I	Н	H1	Weight kg (lbs)	Flow max. I/min. (gpm)
G 1/4	25.5 (1)	13.5 (0.53)	8.5 (0.34)	3 (0.12)	8 (0.32)	10 (0.39)	11 (0.43)	5 (0.2)	1.5 (0.6)	0.011 (0.024)	10 (3)
G 3/8	28 (1.1)	15 (0.59)	10.5 (0.41)	2 (0.08)	11 (0.43)	14 (0.55)	14.5 (0.57)	5 (0.2)	1.5 (0.6)	0.024 (0.053)	16 (4)
G 1/2	35 (1.38)	19.5 (0.77)	13 (0.52)	2 (0.08)	14 (0.55)	17.5 (0.69)	17.5 (0.69)	5 (0.2)	1.5 (0.6)	0.048 (0.106)	40 (11)

*

Ζ

* Thread in accordance with ISO 228-1

0T.F1.01.00

Y

Ordering code

Insert type - Flow control, 2-way pressure compensated

fixed setting

Port sizes = 09 G 1/4 = 02 G 3/8 = 03 G 1/2

Note: available also as"Sleeve valve for line mounting"	
See data sheets RE 18316-12 and RE 18316-1	13

Series 0/A to L unchanged performances and dimensions

		Regulated flow range I/min. (gpm)									
	= 01	= 02	= 03	= 04	= 05	= 06	= 07	= 08	= 09	= 10	
for Y=09	1	2 (0.5) ± 20%									
		5 (1.3) ± 15%							-	-	
for Y=03		16 (4.2) ± 10%						-	-	-	

Туре	Material number	Туре	Material number
0TF101000201000	R931002311	0TF101000306000	R931002063
0TF101000202000	R931002312	0TF101000307000	R931001404
0TF101000203000	R931002313	0TF101000901000	R931002304
0TF101000204000	R931002314	0TF101000902000	R931000010
0TF101000205000	R931000009	0TF101000903000	R931000272
0TF101000206000	R931002315	0TF101000904000	R931002305
0TF101000207000	R931002316	0TF101000905000	R931002306
0TF101000208000	R931002317	0TF101000906000	R931000011
0TF101000301000	R931002318	0TF101000907000	R931002307
0TF101000302000	R931002319	0TF101000908000	R931002308
0TF101000303000	R931002320	0TF101000909000	R931002309
0TF101000304000	R931002321	0TF101000910000	R931002310
0TF101000305000	R931002322		

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Subject to change.

P.O. Box no. 5 41015 Nonantola – Modena, Italy

Bosch Rexroth Oil Control S.p.A.

Tel. +39 059 887 611

Via Leonardo da Vinci 5

Fax +39 059 547 848

compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics