


Cartridge style in manifold

OR.13 - K - X - Y - Z - W

Dimensions



Technical data

Max flow:	up to 120 l/min	(32 gpm)
Max operating pressure for steel body:	350 bar	(5000 psi)
Max operating pressure for aluminium body:	210 bar	(3000 psi)

To order only manifold see data sheet RE 18325-85





Table “Y”

[illegible]

Performance graphs



Ordering code

OR.13	K	X	Y	Z	W
-------	---	---	---	---	---

Manifold with relief direct acting poppet type differential area

Cartridge style - Common cavity
(see table K on page 2)

Cartridge style - Adjustments
(see table X on page 2)

Manifold material

= 00 Aluminium manifold

= S0	Steel manifold
-------------	----------------

Settings - Springs
(see table Z on page 2)

Manifold style - Dimensions and port sizes
(see table Y on page 1)

Preferred types (readily available)

[illegible][illegible]

Further types available by request