

**RE 18329-61/10.19** 1/2 Replaces: RE 18329-61/01.19

# Insert type Check, poppet type



# 0T.U5.01.00 - Y - Z



VUH1

#### Description

When pressure at 1 rises above the spring bias pressure, the poppet is lifted and flow allowed from 1 to 2. The valve is closed (checked) from 2 to 1. Precision machining and hardening processes allow virtually leak-free performance in the checked condition.

Note: UNF and Metric versions available on request. Consult factory.

#### Performance



### Technical data

	Max. operating pressure bar (psi)	350 (5000)						
	Max. flow l/min. (gpm)	see "performance" graph						
n ı	Max. internal drops/min. leakage	5						
	Fluid temperature range °C (°F)	-30 to 100 (-22 to 212)						
	Installation torque Nm (ft-lbs)	see "Dimensions" table						
	Weight kg (lbs)	see "Dimensions" table						
	Special cavity	see "Dimensions"						
	MTTFD	150 years see data sheet 18350-51						
	Lines bodies and standard assemblies	Please refer to section "Hydraulic integrated circuit" or consult factory						
	Seal kit (*) code material no.	see "Dimensions" table						
	- Fluids	Mineral-based or synthetics with lubricating properties at viscosities of 5 to 800 mm²/s (cSt)						
	Recommended degree of fluid contamination	Nominal value max. 10µm (NAS 8) ISO 4406 20/18/15						
	Other Technical Data	See data sheet RE 18350-50						
	*) Only external scale for 10 values							

(\*) Only external seals for 10 valves

#### Dimensions

## Fitting tool dimensions



G *	А	В	С	D	E	F	O-Ring dimensions	Seal kit	Н	I	Weight kg (lbs)	Inst. torque Nm (ft-lbs)	Flow max. l/min.(gpm)
G 1/4	8.5 (0.34)	8.8 (0.35)	4.2 (0.17)	7 (0.28)	2.2 (0.09)	11.6 (0.46)		RG09UH010000100 R931002413		11.3 (0.45)	0.005	15 (11)	20 (5)
G 3/8	10.8	12	7	9	3	15.1		RG02UH010000100		14.8 (0.58)	0.015 (0.033)	20 (15)	50 (13)
G 1/2	14.2 (0.56)		8 (0.32)	12 (0.47)	3.8 (0.15)	18.8 (0.74)	Ø 14x1.5 (0.55x0.06)	RG03UH010000100 R931002412		18.6 (0.73)	0.015 (0.033)	30 (22)	80 (21)
G 3/4	16.5 (0.65)	14.7 (0.58)	7.2 (0.28)	18 (0.71)	5 (0.2)	24.5 (0.96)	Ø 18.77x1.78 (0.74x0.07)	RG04UH010000100 R930076457		23.9 (0.94)	0.036 (0.079)	50 (37)	120 (32)

\* Thread in accordance with ISO 228-1

# Ordering code



Subject to change.