4/3 Proportional directional valve elements with proportional hydraulic control and flow sharing control (LUDV concept)

L85P5... (EDC-IP)

Size 6 ►

- Series 00
- Maximum operating pressure 310 bar (4500 psi) ►
- Maximum flow at 14 bar (203 psi) 50 l/min (13.2 gpm)
- Maximum flow at 18 bar (261 psi) 58 l/min (15.3 gpm)
- ▶ Ports connections planned G 3/8 G 1/2 SAE8 and Modular

<u>NEW</u> spool position sensor available for this valve. See RE18300-30

General specifications

- Valve element with direct proportional flow sharing control.
- It can achieve the simultaneous activation of different actuators by distributing the available flow proportionally to the speeds selected by the operator.
- All simultaneous movements go on at the same reciprocal speed also in case of flow shortage.
- Hydraulically direct operated spool.
- ► Hydraulic operating element bolted on.
- Hydraulic operating element available with inlet port: G1/4 DIN3852; 9/16-18 UNF 2-B.
- The control spool is held in the central position by return springs.

Ordering details	2
Functional description	4
Technical data	5
Characteristic curves	6
External dimensions and fittings	8

rexroth A Bosch Company

RE 18301-14 Edition: 01.2023

Replaces: 04.2016



Ordering details

	01	02	03 5	04	05		06	00	00	07	_			
	L	8	5	P5				00	00		0	00		
amil	у						Port	s						
01	Directi	ional Valve ele	ements ED			L	07	/ -				0		
Гуре							-	G 1/2 DIN				2		
02		proportional				8	J		⁼ 2-B (SAE8) to interface m			3 M ²⁾		
	guratio Flow S					5	┓└──	Machineu						
	ation ty	v				5	 1)	ne required h	ydraulic layou	it and spool y	variant can b	e chosen by		
<u> </u>		hydraulic pro	portional			P5		onsulting pag				o onocon 25		
	l varian								45, RE18301-4	46, RE18301-	47, for flange	eable		
05	4/3 op	erated on botl	h sides a and b	כ;		B2		ements.						
		, T closed in n				02	3) VV	ітп Δр (Р > А	or P > B) 14	oar (203 psi)	•			
	4/3 op P close	erated on bo ed: A and B to	th sides a and o T in neutral	d b;		E2								
Flow		Nominal f					l ▼ s	ymbols						
06	Both m	neter in and c	out, A 4l/min(1,06gpm) -		S 0	┓			т- <u> </u>				
		iin(1,06gpm)	out, A 8l/min(1.85gpm) -				<u>-</u>						
		iin(1,85gpm)	Jut, A Olymmit	1,05gpiii) -		S1				= (n			
	Both n B 12l/ı	neter in and c min(3,17gpm	out, A 12l/min)	ı(3,17gpm) -		S2				¥ = :	2			
	Both m B 16l/ı	neter in and c min(4,23gpm	out, A 16l/min)	1(4,23gpm) -		S 3		12		= ;	3			
	B 25l/ı	min(6,6gpm)	out, A 25l/min			S 4								
	Both meter in and out, A 40l/min(10,57gpm) - B 40l/min(10,57gpm)					S 8								
	Both meter in and out, A 50l/min(13,2gpm) - B 50l/min(13,2gpm)					S9								
	Only meter in, A 8l/min(1,85gpm) - B 8l/min(1,85gpm) Only meter in, A 12l/min(3,17gpm) -					11								
	B 12l/ı	min(3,17gpm				12								
	B 251/r	min(6,6gpm)				14								
	Only meter in, A 40l/min(10,57gpm) - B 40l/min(10,57gpm) Only meter in, A 50l/min(13,2gpm) - B 50l/min(13,2gpm) Both meter in and out, A 4l/min(1,06gpm) - B 8l/min(1,85gpm)					18								
						19								
						01								
	Both meter in and out, A 8l/min(1,85gpm) - B 12l/min(3,17gpm)					12								
	Both meter in and out, A 8l/min(1,85gpm) - B 16l/min(4,23gpm)					13								
	Both meter in and out, A 12l/min(3,17gpm) - B 16l/min(4,23gpm)					23								
	Both meter in and out, A 12l/min(3,17gpm) - B 25l/min(6,6gpm)					24								
	B 25l/ı	min(6,6gpm)	out, A 16l/min			34								
	B 40l/ı	min(10,57gpr	-			38								
	B 40l/ı	min(10,57gpr	-			48								
	B 50l/ı	min(13,2gpm	-			49								
		neter in and c min(13,2gpm	out, A 40l/min)	ı(10,57gpm) -		89								

Spool variant and Flow pattern

Both meter in and out





Only meter in



4 **L85P5... (EDC-IP)** | 4/3 Proportional directional valve elements Functional description

Functional description



The sandwich plate design directional valve elements L85P5... are compact direct hydraulic operated pressure compensated proportional valves which control the start, the stop, the direction and the quantity of the oil flow, with FLOW SHARING principle. These elements basically consist of a stackable housing (1) with a control spool (2), two hydraulic operating blocks (4), and two return spring return (3).

The hydraulic pressure in one of the blocks (4) pushes the control spool (2) from its neutral-central position "0" to the required end position "a" or "b". When the spool is shifted and the metering notch is open, flow delivery starts and is controlled by a 3 way pressure compensator followed by a check valve for each port A and B.

The compensator, balanced by the LS pressure at the opposite end, lifts up and unloads a regulated flow which is sent to the A (or B) port through the relevant check valve; at the same time the opposite port allows oil return to tank. LS pressure reaches the compensator "dead end" directly from the A or B port, while the check valves lock eventual pressure oscillations which could affect the compensator function.

When the pressure decrease in one of the block (4), the return spring (3) pushes the spool thrust washer back against the housing and the spool returns in its neutral-central position.

Technical data

General		
Valve element with 2 hydraulic controls	kg (lbs)	3.05 (6.72)
Ambient Temperature	°C (°F)	-20+50 (-4+122) (NBR seals)
Hydraulic		
Maximum pressure at P, A and B ports	bar (psi)	310 (4500)
Maximum pressure at T to prevent damages	bar (psi)	100 (1450)
Reccomended maximum pressure at T during operation	bar (psi)	10 (145)
Max. pilot pressure	bar (psi)	35 (508)
Min. pilot pressure		refer to page 6
Max. regulated flow at 14 bar (203 psi)	l/min (gpm)	50 (13.2)
Max. regulated flow at 18 bar (261 psi)	l/min (gpm)	58 (15.3)
E-schemes flow pattern symmetrical closed pass in the neutral position (connection from A to T and B to T)		Approx. 2% of the nominal cross-section
Hydraulic fluid General properties: it must have physical lubricating and chemical properties suitable for use in hydraulic systems such as, for example:		Mineral oil based hydraulic fluids HL (DIN 51524 part 1). Mineral oil based hydraulic fluids HLP (DIN 51524 part 2). For use of environmentally acceptable fluids (vegetable or polyglycol base) please consult us.
Fluid Temperature	°C (°F)	-20+80 (-4+176) (NBR seals)
Permissible degree of fluid contamination		ISO 4572: β _x ≥75 X=1012 ISO 4406: class 19/17/14 NAS 1638: class 8
Viscosity range	mm²/s	20380 (optimal 3046)

Note

For applications with different specifications consult us

Characteristic curves







Pressure drop $\Delta p = \Delta p(Q)$ (P_{IN}- P_{OUT}) to the next section



Pressure drop $\Delta p = \Delta p(Q)$ with spool B2S9



The curves refer to the spool fully open. Measured with hydraulic fluid ISO-VG32 at 45° ±5 °C (113° ±9 °F); ambient temperature 20 °C (68 °F). 8 **L85P5... (EDC-IP)** | 4/3 Proportional directional valve elements External dimensions and fittings

External dimensions and fittings



- 1 Hydraulic operating element available with inlet port: G1/4 DIN3852; 9/16-18 UNF 2-B (SAE6)
- 2 Flange specifications for coupling to ED intermediate elements.
- **3** For tie rod and tightening torque information see data sheet RE 18301-90
- 4 A and B ports.

Bosch Rexroth Oil Control S.p.A.

Oleodinamica LC Division Via Artigianale Sedrio, 12 42030 Vezzano sul Crostolo Reggio Emilia - Italy Tel. +39 0522 601 801 Fax +39 0522 606 226 / 601 802 compact-hydraulics-cdv@boschrexroth.com www.boschrexroth.com/compacthydraulics

- 5 Identification label.
- **6** Four threaded holes M5 deepth 12mm [0.47 inch] for fitting a secondary flangeable element. Bolts M5 with recommended strength class DIN8.8: torque 5-6 Nm[3.6-4.4 ft-lb] (only for version with modular secondary valves).

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Subject to change.