

# Directional spool valve, direct-operated, with solenoid actuation **FTWE 2 K**



- ▶ Size 2
- ▶ Series 3X
- ▶ Maximum working pressure 100 bar
- ▶ Maximum flow 2 l/min

## Features

- ▶ 3/2-way version
- ▶ Cartridge valve
- ▶ Minimized frame size
- ▶ DC voltage solenoid switching in oil
- ▶ Electrical connection as single connection
- ▶ With manual override
- ▶ For use in vehicles and mobile working machines

## Contents

Type code	2
Preferred types	2
Functional description	3
Technical data	4
Characteristic curves	5
Dimensions	6
Mounting cavity	7
Available individual components	8
Related documentation	8

Type code

01	02	03	04	05	06	07	08	09	10	11
FTWE	2	K		3X	/	100	A		V	*

Valve type

01	Directional spool valve, non-standard design, electrical actuation	FTWE
02	Size 2	2
03	Cartridge valve	K
04	Switching characteristics (others on request)	C

Series

05	Series 30 to 39 (unchanged installation and connection dimensions)	3X
----	--	----

Maximum nominal pressure

06	100 bar	100
----	---------	-----

07	DC voltage solenoid, switching in oil	A
----	---------------------------------------	---

Supply voltage

08	Control electronics 12 V DC	G12
	Control electronics 24 V DC	G24

Electrical connection<sup>1)</sup>

09	Device connector 2-pin, DT 04-2P (DEUTSCH)	K40
	Device connector 2-pin, Junior Timer (AMP) <sup>2)</sup>	C4

Sealing material

10	FKM (fluorocarbon rubber)	V
11	Further details in plain text	*

Notice

For valve types other than those listed in the data sheet, consultation is required!

Preferred types

Type	Material no.
FTWE 2 KC3X/100AG12C4V	R900578533
FTWE 2 KC3X/100AG12K40V	R901047340
FTWE 2 KC3X/100AG24C4V	R900578535
FTWE 2 KC3X/100AG24K40V	R901032720

1)

Plug-in connectors are not included in the scope of delivery and must be ordered separately, see data sheet 08006.

2)

Manual override can only be performed after disconnecting the device plug!


## Functional description

### General


The Directional spool valve type FTWE 2 K is a direct-operated, pressure-balanced cartridge valve in 3-way version.

It controls the start, stop and direction of a flow.

#### ▼ Version "C" (Standard)



#### ▼ Version "U" (Special version)



### Basic principle

In non-actuated state, the control spool (2) is kept in the initial position by the return spring.

- ▶ Version "C" (standard)
  - Initial position from **A** → **T**
  - When actuated, the valve opens from **P** → **A**
- ▶ Version "U" (special version, on request)
  - Initial position from **P** → **A**
  - When actuated, the valve opens from **A** → **T**


The control spool (2) is actuated by a DC voltage solenoid (1) switching in oil. The **A** and **P** ports can be permanently loaded with 100 bar working pressure, port **T** with a maximum of 30 bar.

### Notice

Special versions (e.g. symbol "U") on request.

Special installation drawings apply to all special versions.

### ▼ Section



<sup>1)</sup> Actuated by pin tool (connector must be removed to actuate manual override; versions "C4" and "K40"). Maximum number of matings is 10 (Specification AMP 108-18013).

## Technical data

General					
Weight (approx.)		kg	0.16		
Installation position			Any		
Ambient temperature range		°C	−30 ... +80		
Salt spray test according to ISO 9227		h	600 (NSS test)		
Solenoid surface protection		Coating according to DIN 50962-Fe//ZnNi with thick film passivation			
Hydraulic					
Maximum working pressure	Port <b>A</b>	$p_A$	bar	100	
	Port <b>P</b>	$p_P$	bar	100	
Max. counter-pressure	Port <b>T</b>	$p_T$	bar	30	
Maximum flow ( $\Delta p = 5$ bar)	<b>P</b> → <b>A</b>	$q_v$	l/min	2	
Maximum leakage flow	Port <b>T</b>	$q_L$	cm³/min	≤ 60 ( $p_P = 50$ bar; control current $I = 0$ )	
Hydraulic fluid			See table on page 5		
Hydraulic fluid temperature range		$\vartheta$	°C	−30 ... +80	
Viscosity range		$\nu$	mm²/s	10 ... 380	
Maximum admissible degree of contamination of hydraulic fluid, cleanliness level as per ISO 4406 (c)				Level 20/18/15 <sup>1)</sup>	
Load cycles				10 million	
Electric					
Voltage type			DC voltage		
Supply voltage (±15 %)		$U$	V	<b>12</b>	<b>24</b>
Power consumption	at 20 °C	$P$	W	14.4	14.4
Coil resistance	Cold value at 20 °C	$R$	Ω	10	40
Duty cycle			%	100	
Maximum coil temperature <sup>2)</sup>			°C	150	
Switching time	ON		ms	≤20	
	OFF		ms	≤30	
Type of protection according to ISO 20653	Connector version "C4"		IP6K5 <sup>3)</sup>		
			IP6K7 and IP6K9K <sup>3)</sup> (only with Rexroth plug-in connector, material no. R901022127)		
	Connector version "K40"		IP6K7 and IP6K9K <sup>3)</sup>		
Switching frequency			Hz	5	
Design according to VDE 0580					

### Notice

- ▶ For applications outside these values, please consult us!
- ▶ The technical data was determined at a viscosity of  $\nu = 46$  mm<sup>2</sup>/s (HLP46;  $\vartheta_{oil} = 40$  °C).

### Notice

For the electrical connection, a protective earth (PE  $\perp$ ) connection is mandatory based on the specification.

1) Cleanliness levels specified for the components must be maintained in the hydraulic systems. Effective filtration prevents malfunctions and simultaneously extends the service life of the components.  
We recommend a filter with a minimum retention rate of  $\beta_{10} \geq 75$ .

2) Surface temperature > 50 °C possible, provide contact protection in compliance with ISO 13732-1 and ISO 4413 standards.  
3) With assembled and locked plug-in connector

## Hydraulic fluid

Hydraulic fluid		Classification	Suitable sealing materials	Standards	Data sheet
Mineral oils		HL, HLP	FKM	DIN 51524	90220
Environmentally acceptable	Insoluble in water	HEES	FKM	ISO 15380	90221
	Soluble in water	HEPG	FKM	ISO 15380	90221


### Notice

- Further information and details on using other hydraulic fluids are available in the above data sheets or on request.
- Restrictions are possible with the technical valve data (temperature, pressure range, service life, maintenance intervals, etc.)!


- The flash point of the hydraulic fluid used must be 40 K above the maximum solenoid surface temperature.
- **Environmentally acceptable:** If environmentally acceptable hydraulic fluids are used that are also zinc-soluble, there may be an accumulation of zinc.

## Characteristic curves

**$\Delta p$ - $q_v$  flow characteristic curve** ( $q_v$  = minimum specification)  
**P → A; A → T**



**Performance limit**




### Notice


Characteristic curves measured with HLP46,  
 $\vartheta_{oil} = 40 \pm 5 \text{ } ^\circ\text{C}$ .

## Dimensions

▼ **FTWE 2 K with screw-in thread**



- |  |  |
|--|--|
| <ol style="list-style-type: none"> <li><b>1</b> Device connector "K40"<br/>(separate order, see data sheet 08006)</li> <li><b>2</b> Device connector "C4"<br/>(separate order, see data sheet 08006)</li> <li><b>3</b> Hexagon SW27; tightening torque <math>M_A = 10+5</math> Nm</li> </ol> | <ol style="list-style-type: none"> <li><b>4</b> Manual override:<br/>Actuated by pin tool (connector must be removed to actuate manual override; versions "C4" and "K40"). Maximum number of matings is 10 (Specification AMP 108-18013).</li> <li><b>5</b> Version "C" (standard)</li> <li><b>6</b> Version "U" (on request)</li> </ol> |
|--|--|


**Mounting cavity****Standards:**

Workpiece edges	ISO 13715
Shape and position tolerance	ISO 1101
General tolerances for machining	ISO 2768-mK
Tolerance	ISO 8015
Surface finish	ISO 1302

- 1) Depth of fit
- 2) All seal ring insertion faces are rounded and free of burrs
- 3) Required roughness up to  $\varnothing 25.5$  mm
- 4) Required evenness up to  $\varnothing 25.5$  mm
- 5) Required roughness from 11.5 ... 13.4 mm
- 6) Stepped beveling available
- 7) Version "C" (standard)
- 8) Version "U" (on request)

Available individual components

▼ FTWE 2 K with screw-in thread



Item	Denomination	Material no.
999	Seal kit of the valve (FKM)	R961007176

Seal kits with other seals on request.

Related documentation

- |   |            |                                 |
|---|------------|---------------------------------|
| ▶ Control electronics:                        |            |                                 |
| – Analog amplifier                            | Type RA... | Data sheet 95230                |
| – BODAS controller                            | Type RC... | Data sheets 95204, 95205, 95206 |
| ▶ Mineral oil-based hydraulic fluids          |            | Data sheet 90220                |
| ▶ Environmentally acceptable hydraulic fluids |            | Data sheet 90221                |
| ▶ MTTF <sub>p</sub> values                    |            | Data sheet 90294                |

**Bosch Rexroth AG**  
Zum Eisengießer 1  
97816 Lohr am Main  
Germany  
Phone +49 9352 18-0  
info.ma@boschrexroth.de  
www.boschrexroth.com

© Bosch Rexroth AG 2021. All rights reserved, also regarding any disposal, exploitation, reproduction, editing, distribution, as well as in the event of applications for industrial property rights. The data specified within only serves to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.