## rexroth A Bosch Company

# Solenoid operated valves pilot operated poppet type 2-way normally closed proximity sensor with overlapping Common cavity, Size 08

VESP-08A-12A/00-2A05-N7

### OD.15.05.18.41 - Y - Z





#### ▼ Version 05/06/07









General			
Weight		0.13 kg (0.29 lbs)	
Installation orientation		Optional	
Ambient temperature range		-25 to 60 °C (-13 to 140 °F)	
Hydraulic			
Max. operating pressure		350 bar (5000 psi)	
Flow range		1 - 40 l/min (0.3 - 11 gpm)	
Max. internal leakage		15 drops/min.	
Fluid temperature range		-20 to 80 °C (-4 to 176 °F)	
Fluids: Mineral-based o viscosities of 15 to 380	-	ith lubricating properties at	
Installation torque		30 - 35 Nm (22 - 26 ft-lbs)	
Recommended degree of fluid contamination		Nominal value max. 10 μm (NAS 8) ISO 4406 19/17/14	
MTTFD		150 years see RE 18350-51	
DC		99% * according to ISO 13849-1/2	
Common cavity		CA-08A-2N see 18325-70	
Lines bodies and standard assemblies		Please refer to section "Hydaulic integrated circuit" or consult factory	
Seal kit	code material no.	RG08A2010520100 R901101437	
Other technical data		See data sheet 18350-50	
Electrical			
Type of voltage		DC voltage	
Coil type		S8-356 see 18325-90	
Supply voltage		See data sheet 18325-90	
Nominal voltage		± 10%	
Power consumption		20 W	
Duty cycle coil		100 % see 18325-90	
T	Type of protection		

Please consider that a proper fuction of the valve is guaranteed only if the position of the monitor is not modified; each cartridge is provided of a torque confirmation mark, intended as antitampering device.

Sensor is protected against short circuit polarity inversion.

\* For more details contact factory

#### Ordering code



Туре	Material number	Туре	Material number
OD1505184105OC	R934004319	OD1505184185OB	R930063653
OD1505184185OC	R934004320		
OD1505184106OC	R934004812		
OD1505184105OB	R930053982		
OD1505184107OC	R930069632		
-			

#### **Characteristic curves**









#### Sensor data:

	24 V DC
Supply voltage	20 to 32
Output load	≤ 400 mA





#### Dimensions

 Version 05-06-85: Solenoid operated valve, poppet 2-way normally closed proximity sensor



### Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola - Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.