Directional control valves pneumatic operated poppet 2-way normally closed Special cavity, 021-E

VPI-8A-2A-12-NC



▼ Version 31



▼ Version 05



▼ Version 11

4AAI

OD.65 - X - 21.14.00

Technical data

RE 18326-76 Edition: 12.2021 Replaces: 05.2020

General					
Weight		0.5 kg (1.1 lbs)			
Installation orientation	Optional				
Ambient temperature range		-30 to 60 °C (-22 to 140 °F)			
Hydraulic					
Max. operating pressure		350 bar (5000 psi)			
Max. flow		150 l/min (40 gpm)			
Max. internal leakage		20 drops/min.			
Fluid temperature range		-20 to 80 °C (-4 to 176 °F)			
Fluids: Mineral-based or synthetics with lubricating properties at viscosities of 20 to 380 mm ² /s (cSt)					
Installation torque		130-150 Nm (96-111 ft-lbs)			
Recommended degree of fluid contamination		Nominal value max. 25 µm (NAS 8) ISO 4406 19/17/14			
MTTFD		150 years see RE 18350-51			
Special cavity		021-E see 18325-75			
Lines bodies and standard assemblies	Please refer to section "Hydraulic integrated circuit" or consult factory				
Seal kit – version 05-11	code material no.	RG21E201052010 R934003566			
Seal kit – version 31	code material no.	RG21E201053010 R934003567			
Other technical data		See data sheet 18350-50			

IMPORTANT: When valve is not operated, flow from 1 to 2 is not recommended due to high opening pressure. (version 05)

ilot	pressure
ilot	pressure

bar (psi) Max. 15 (218) bar (psi) Min. 4 (58)



Preferred types

Туре	Material number	Туре	Material number
OD650521140000	R901166202		
OD653121140000	R934001459		
OD651121140000	R934001456		

Characteristic curves



Dimensions

▼ Version 05: Directional control valves pneumatic operated poppet 2-way normally closed - Special cavity



▼ Version 31: Directional control valves pneumatic operated poppet 2-way double lock normally closed - Special cavity



▼ Version 11: Directional control valves pneumatic operated poppet 2-way normally closed - Special cavity

Ø 34 (1.34)



© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging. Subject to change.

Bosch Rexroth Oil Control S.p.A.

Via Leonardo da Vinci 5 P.O. Box no. 5 41015 Nonantola - Modena, Italy Tel. +39 059 887 611 Fax +39 059 547 848 compact-hydraulics-cv@boschrexroth.com www.boschrexroth.com/compacthydraulics