

Flow control, 3-way pressure compensated combination type fully adjustable


Common cavity

Cartridge style in manifold

VRFD-10A / VRFD-12A - C

ON.06 - K - X - Y - Z - W

Dimensions



Technical data

Flow: adjustable (see table "Z" and performance graph)

Max operating pressure
for **steel** body: 350 bar (5000 psi)

Max operating pressure
for **aluminium** body: 210 bar (3000 psi)

To order only manifold see data sheet RE 18325-85





Table “Y”

[illegible]

Cartridge style



[mm (inches)]

Table “K”

			K				
CARTRIDGE CODE	04	04	02	X	85	Z	VRFD-10A
	04	04	04	X	57	Z	VRFD-12A

Table “X”

X	ADJUSTMENTS	
40	Calibrated handknob (only for K=02)	
04	Handknob	
03	Leakproof hex. socket screw (only for K=04)	

CARTRIDGE TECHNICAL DATA



Common cavity: **CA-10A-3N, CA-12A-3N**
For other details see data sheet RE 18321-20
and RE 18321-21

Table “Z”



[illegible]

Performance graphs

SIZE 10



SIZE 12



Ordering code

ON.06		K	X	Y	Z	W
Manifold with flow control, 3-way pressure compensated combination type fully adjustable						Manifold material
						= 00 Aluminium manifold
						= S0 Steel manifold
Cartridge style - Common cavity (see table K on page 2)						Settings - Regulated flow range (see table Z on page 2)
Cartridge style - Adjustments (see table X on page 2)						Manifold style - Dimensions and port sizes (see table Y on page 1)

Preferred types (readily available)

Type	Material number	Type	Material number
ON0602040220S0	R934001276		
ON0602040240S0	R934001277		
ON0604040450S0	R934003540		
ON060204022000	R934003779		

Further types available by request