

RE 18330-07/04.23

Replaces: RE 18330/07.18

Pressure reducing, pilot operated spool type


Common cavity

Cartridge style in manifold

VRPP-C

OR.07 - K - X - Y - Z - W

Dimensions



Technical data

Max flow:	up to 100 l/min	(26 gpm)
Max operating pressure for steel body:	350 bar	(5000 psi)
Max operating pressure for aluminium body:	210 bar	(3000 psi)

To order only manifold see data sheet RE 18325-85






Table “Y”

[illegible]

Performance graphs



Ordering code

OR.07

Manifold with pressure reducing, pilot operated spool type

Cartridge style - Common cavity (see table K on page 2)

Cartridge style - Adjustments (see table X on page 2)

Manifold material

= 00

Aluminium manifold

= S0

Steel manifold

Settings - Springs

(see table Z on page 2)

Manifold style - Dimensions and port sizes

(see table Y on page 1)

Preferred types (readily available)

Type	Material number	Type	Material number
OR0706030310S0	R934001661		
OR0706030320S0	R934002152		
OR0708030410S0	R934002297		
OR0708030420S0	R934002303		
OR0708030435S0	R934002535		

Further types available by request