

4/3 Directional valve elements with manual lever operated control and with or without LS connections

L8_L1... (ED-LV)

RE 18301-08 Edition: 02.2016 Replaces: 07.2012



Size 6 Series 00 Maximum operating pressure 310 bar (4500 psi) Maximum flow 60 l/min (15.8 gpm) Port connections G 3/8 - G 1/2 - SAE8

General specifications

Valve elements 4 ways 3 positions. Control spools manual operated by hand lever. Control spool with return spring or mechanical detent for all three positions.

Contents

Ordering details	2
Functional description	3
Technical data	4
Characteristic curves	5
External dimensions and fittings	6

Ordering details

01	02	03	04	05	06	07	08	09	10	
L	8		L1							0
Fami	ly									
01	Directi	ional V	alve el	ement	s ED					L
Туре									_	
02	Size 6									8
Confi	iguratio	n								
03	Standa	ard								0
	With L	oad Se	ensing	contro	bl					4
Oper	ation ty	/pe								
04	Manua	ıl lever								L1
Spoo	l varian	ts								
05	4/3 4 \	ways ar	nd 3 po	osition	S					_2
Flow	pattern	1								
06	Both n		n and o	out 1)						S
Nomi	nal flov	v ²⁾							F	
07	18 l/m	in (5.7	5 gpm)						4 ³⁾
	40 l/min (10.6 gpm)							8		
Side	with th	e cont	rol lev	er						
08	a side	with h	andle	aiming	high (A and	B dire	ction)		A0
	a side	with ha	andle a	iming l	ow (op	oposite	e to A a	nd B)		A2
	b side	with h	andle	aiming	; high (A and	B dire	ction)		B0
	b side			aiming	glow (opposi	te to A	and E	3)	B2
Manu	al leve	r contr	ol						r	
09	With re									M1
	With m	nechan	ical de	etent fo	or all t	nree p	osition	S		F1
Ports									F	
10	G 3/8									0
	G 1/2									2
	3/4-16	UNF 2	2-B (SA	AE8)						3

Symbols







Side with the control lever



$$\begin{array}{c|c} A & B \\ \hline a & 0 & b \\ \hline P & T \end{array} = 2S_A_F1_{-}$$

$$\begin{array}{c|c} A & B \\ \hline a & 0 & b \\ \hline P & T \end{array} = 2S_B_M1_{-}$$

$$\begin{array}{c|c} A & B \\ \hline a & 0 & b \\ \hline P & T \end{array} = 2S_B_F1_{-}$$

1) Only meter in for E2S8 spool variant

²⁾ With Δp (P > T) 10 bar (145 psi), corresponding approx.

to $\Delta p P > A, B 5$ bar (73 psi). 3) Available only for B_, E_ spool variants.

Functional description



The sandwich plate design directional valve elements L8_1... are compact manual operated valves which control the start, the stop and the direction of the oil flow.

These elements basically consist of a stackable housing (1) with a control spool (2), a block with the control lever (3), and a spring housing (4) with a return spring (5).

The hand operated lever moves the control spool (2) from its neutral-central position "0" to the required position "a" or "b", and the required flow from P to A (with B to T), or P to B (with A to T) is achieved.

Type L8_L1_2S___M100 is the valve version in which the return spring (5) brings the spool back to neutral-central

position "0" when the manual lever is not operated. The valve is available with a choice of spool variants (refer to page 2).

Type L8_L1_2S___F100 is the valve version with mechanical detent in which the control spool (**2**) stays in anyone of the 3 achieved positions "0", "a" or "b" when the lever is left free. With this valve, the oil delivery can continue without any action on the lever.

Also this version is available with a choice of spool variants (refer to page 2).

Special types of control are available upon request.

4 **L8_L1... (ED-LV)** | 4/3 Directional valve elements Technical data

Technical data

General						
Valve element weight	kg (lbs)	1.55 (3.42)				
Mounting position	kg (lbs)	Unrestricted				
Ambient Temperature	°C (°F)	-20+50 (-4+122) (NBR seals)				
Hydraulic						
Maximum pressure at P, A and B ports	bar (psi)	310 (4500)				
Maximum pressure at T	bar (psi)	160 (2320)				
Maximum inlet flow	l/min (gpm)	60 (15.9)				
Nominal flow with DP P>T = 10 bar (145 psi)	l/min (gpm)	10, 20, 30 (2.64, 5.28, 7.9)				
Hydraulic fluid General properties: it must have physical lubricating and chemical properties suitable for use in hydraulic systems such as, for example:		Mineral oil based hydraulic fluids HL (DIN 51524 part 1). Mineral oil based hydraulic fluids HLP (DIN 51524 part 2). For use of environmentally acceptable fluids (vegetable or polyglycol base) please consult us.				
Fluid Temperature	°C (°F)	-20+80 (-4+176) (NBR seals)				
Permissible degree of fluid contamination		ISO 4572: β _x ≥75 X=1215 ISO 4406: class 20/15/15 NAS 1638: class 9				
Viscosity range	mm²/s	5420				

Note

For applications with different specifications consult us

Characteristic curves



 A2S8
 3
 3
 3
 3
 1

 B2S4, E2S4
 1
 1
 5
 5

Measured with hydraulic fluid ISO-VG32 at 45° \pm 5 °C (113° \pm 9 °F); ambient temperature 20 °C (68 °F).

Performance limits



Curve no.

1



A2S8, B2S8, E2S8, B2S4, E2S4

Minimum flow for efficiency of LS control



6 **L8_L1... (ED-LV)** | 4/3 Directional valve elements External dimensions and fittings

External dimensions and fittings



- 4 Flange specifications for coupling to ED intermediate elements with ports G 3/8.
- **5** For tie rod and tightening torque information see data sheet RE 18301-90.
- **6** Flange specifications for coupling to ED intermediate elements with ports G 1/2 (SAE 8).
- 7 A and B ports.
- 8 Side with the control lever (Standard is side A).

- 9 Hand lever orientation.
- **10** Hand lever orientation for packing and shipment.
- 11 Identification label.
- 12 LS channel (only for versions L84...).
- **13** Four threaded holes for fitting a secondary flangeable elements: - M5 holes on versions with ports G 3/8.
 - M6 holes on versions with ports SAE 8.
 - Without when the ports is G 1/2.

Bosch Rexroth Oil Control S.p.A.

Oleodinamica LC Division Via Artigianale Sedrio, 12 42030 Vezzano sul Crostolo Reggio Emilia - Italy Tel. +39 0522 601 801 Fax +39 0522 606 226 / 601 802 compact-hydraulics-cdv@boschrexroth.com www.boschrexroth.com/compacthydraulics © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Oil Control S.p.a.. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Subject to change.