Rexroth Bosch Group

# 2/2 proportional directional valve, direct operated

**RE 18139-09/12.11** 1/10 Replaces: 04.09

Type KKDS (High Performance)

Component size 2 Component series A Maximum operating pressure 350 bar Maximum flow 58 l/min



# Table of contents

Contents	Page
Features	1
Ordering code	2
Preferred types	2
Function, section, symbol	3
Technical data	4, 5
Characteristic curves	6
Limits of performance	6
Minimum terminal voltage at the coil	
and relative duty cycle	7
Unit dimensions	8
Mounting cavity	9
Available individual components	10

#### Features

ge	<ul> <li>Cartridge valve</li> </ul>	
1	<ul> <li>Mounting cavity R/T-5A</li> </ul>	
2	- Direct operated proportional valve for contr	olling the flow size
2 3	<ul> <li>Operation by means of proportional solenoi thread and detachable coil</li> </ul>	id with central
I, 5	<ul> <li>Rotatable solenoid coil</li> </ul>	
6	- With concealed manual override, optional	
6	<ul> <li>Control electronics:</li> </ul>	Data sheet
7	<ul> <li>Proportional plug-in amplifier type VT-SSPA1</li> </ul>	30116
8	Analog amplifier type RA	95230
9		
10		

Information on available spare parts: www.boschrexroth.com/spc

# Ordering code



# **Preferred types**

Туре	Material no.
KKDSR2NA/HCG24N9K4V	R901074596
KKDSR2NA/HCG12N9K4V	R901036359
KKDSR2NA/HCG24N9C4V	R901055340

## Function, section, symbol

#### General

The 2/2 proportional directional valve is a direct operated cartridge spool valve. It regulates the flow proportionally to the input signal in a continuous form from main port (1) to (2).

The valve basically comprises of a bushing (6) with male thread for the mounting cavity, socket (3), control spool (5) with compression spring (8) as well as proportional solenoid (7) with central thread and removable coil.

#### Function

With de-energized solenoid (7), the control spool (5) that is always pressure-compensated to the actuating forces due to its constructive design is held in the initial position by the compression spring (8) and blocks the flow between main port (1) and (2). By energizing the solenoid (7), the control spool (5) is directly adjusted – proportional to the electric input signal – and, via orifice-like cross-sections with progressive flow characteristic in the spool, connects the main ports (1) and (2). Upon de-excitation of the solenoid (7), the control spool (5) is brought back into the initial position by the compression spring (8).

The manual override (4) allows for the switching of the valve without solenoid energization.



Symbol



Type KKDSR2NA/HC.N9K4V

# Technical data (For applications outside these parameters, please consult us!)

Weight	kg	0.84
Installation position		Any – if it is ensured that no air can collect upstream the valve. Otherwise, we recommend suspended installation o the valve.
Ambient temperature range	°C	-40 to +100 (see Minimum terminal voltage page 7)
Storage temperature range	°C	-20 to +80
Environmental audits		
Salt spray test according to DIN 50021	h	720
Surface protection Proportional solenoid		Coating according to DIN 50962-Fe//ZnNi with thick lay- er passivation

#### hydraulic

Maximum operating pre	essure ba	r 350
Maximum flow	l/mi	1 58
Leakage	ml/mi	$  < 60 \text{ (with } \Delta \boldsymbol{p} = 100 \text{ bar in } (1); \text{ HLP46, } \vartheta_{\text{oil}} = 40 \text{ °C})$
Step response	0 to 100 %; 100 to 0 % m	$ < 180 \text{ (with } \boldsymbol{p}_{\text{S}} = 10 \text{ bar)}$
Hydraulic fluid		See table page 5
Hydraulic fluid tempera	ture range °(	C -40 to +100 (preferably +40 to +50)
Viscosity range	mm²/	s 5 to 400 (preferably 10 to 100)
	gree of contamination of the hydraulic according to ISO 4406 (c)	Class 20/18/15 1)
Hysteresis 2)	9	‰ ≤ 5
Range of inversion <sup>2)</sup>	9	6 ≤ 2
Response sensitivity 2)	9	6 ≤ 1
Load cycles		10 million

<sup>1)</sup> The cleanliness classes specified for the components must be adhered to in hydraulic systems. Effective filtration prevents faults and at the same time increases the service life of the components.

For the selection of the filters see

www.boschrexroth.com/filter.

<sup>2)</sup> Measured with analog amplifier type RA2-1/10, see data sheet 95230.

# Technical data (For applications outside these parameters, please consult us!)

#### hydraulic

Hydraulic fluid		Classification	Suitable sealing materials	Standards	
Mineral oils and related hydrocarbons		HL, HLP, HLPD, HVLP, HVLPD	FKM	DIN 51524	
Environmentally compatible	- Insoluble in water	HEES	FKM	100 15000	
		HEPR	FKM	- ISO 15380	
	<ul> <li>Soluble in water</li> </ul>	HEPG	FKM	ISO 15380	
Flame-resistant	- Water-free	HFDU, HFDR	FKM	ISO 12922	
	- Water-containing	HFAS	FKM	ISO 12922	

ids!
l

- For more information and data on the use of other hydraulic fluids refer to data sheet 90220 or contact us!
- There may be limitations regarding the technical valve data (temperature, pressure range, service life, maintenance intervals, etc.)!
- The flash point of the process and operating medium used must be 40 K higher than the maximum solenoid surface temperature.
- Flame-resistant water-containing: Maximum pressure differential per control edge 175 bar, otherwise, increased cavitation erosion!

Tank pre-loading < 1 bar or > 20 % of the pressure differential. Pressure peaks should not exceed maximum operating pressures!

- **Environmentally compatible:** When using environmentally compatible hydraulic fluids that are simultaneously zinc-solving, zinc may accumulate in the medium (700 mg zinc per pole tube).

#### electric

Voltage type		Direct voltage (DC)			
Supply voltage V		12	24		
Maximum solenoid current A		1.8	1.2		
Coil resistance	<ul> <li>Cold value at 20 °C</li> </ul>	Ω	3.3	7.2	
	<ul> <li>Max. hot value</li> </ul>	Ω	5.8	13.0	
Switch-on duration %		6 100 (see minimum terminal voltage page 7)			
Maximum coil temperature	Aximum coil temperature 3) °C		150		
Protection class according	<ul> <li>Version "K4"</li> </ul>		IP 65 with mating connector mounted and locked		
to DIN EN 60529	– Version "K40"		IP 69K with mating connector mounted and locked		
	- Version "C4"		IP 66 with mating connector mounted and locked		
			IP 69K with Rexroth mating connector (Material no. R901022127)		
Control electronics (separate order)		<ul> <li>Proportional plug-in amplifier type VT-SSPA1, see data sheet 30116</li> </ul>			
		- Analog amplifier type RA, see data sheet 95230			
Design according to VDE 0580					

<sup>3)</sup> Due to the surface temperatures of the solenoid coils, the standards ISO 13732-1 and EN 982 need to be adhered to!

In the electrical connection, the protective earthing conductor (PE  $\frac{1}{2}$ ) must be connected properly.

# **Characteristic curves** (measured with HLP46, $\vartheta_{oil} = 40 \pm 5$ °C)



# **Limits of performance** (measured with HLP46, $\vartheta_{oil} = 40 \pm 5 \text{ °C}$ )



# Minimum terminal voltage at the coil and relative duty cycle

# Admissible working range against the ambient temperature



Limited valve performance

#### IF Notice!

The characteristic curves have been determined for coils with valve with medium test block size (80 x 80 x 80 mm), without flow in calm air.

Depending on the installation conditions (block size, flow, air circulation, etc.) there may be a better heat dissipation. This increases the area of application.

In single cases, more unfavorable conditions may lead to limitations of the range of application.

# Unit dimensions (dimensions in mm)



(1) = Main port 1

- (2) = Main port 2
- LS = Location Shoulder
  - 1 Mating connector without circuitry for connector "K4" (separate order, see data sheet 08006)
  - 2 Space required for removing the mating connector
  - 3 Concealed manual override "N9"
  - 4 SW36, tightening torque  $M_A = 60$  to 65 Nm
  - 5 Mating connector for connector "C4" (separate order, see data sheet 08006)
  - 6 Mating connector for connector "K40" (separate order, see data sheet 08006)

# Mounting cavity R/T-5A<sup>1</sup>; 2 main ports; thread 1-14 UNS-2B (dimensions in mm)





(1) = Main port 1

(2) = Main port 2

LS = Location Shoulder

- <sup>1)</sup> Differing from T-5A
- <sup>2)</sup> Depth for moving parts
- <sup>3)</sup> With counterbore

All seal ring insertion faces are rounded and free of burrs Tolerance for all angles  $\pm 0.5\,^{\circ}$ 

#### Standards:

Workpiece edges	DIN ISO 13715
Form and position tolerance	DIN EN ISO 1101
General tolerances for metal-cutting procedures	DIN ISO 2768-mK
Tolerance	DIN ISO 8015
Surface quality	DIN EN ISO 1302

# Available individual components



Item	Denomination		Direct voltage	Material no.
157	Coil for individual connection	Version "K4"	12 V	R901022180
			24 V	R901022174
		Version "K40"	12 V	R901272648
			24 V	R901272647
		Version "C4"	12 V	R901022680
			24 V	R901022683
158	Nut			R900029574
159	O-ring for pole tube			R900002507
999	Seal kit of the valve			R961004435

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52 / 18-0 Fax +49 (0) 93 52 / 18-23 58 documentation@boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

## Notes

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52 / 18-0 Fax +49 (0) 93 52 / 18-23 58 documentation@boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52 / 18-0 Fax +49 (0) 93 52 / 18-23 58 documentation@boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.